

PHILIPS

Beard trimmer

Beardtrimmer series
5000

0.2mm precision settings

Self-sharpening metal blades

90 min cordless use/1h charge

Lift & Trim PRO system



BT5515/13



Even length at every angle

2x more precision with Lift & Trim PRO system

The even and precise trim you want when creating your 3-day stubble, short or long beard look. Our innovative Lift & Trim PRO system lifts the hairs up to the level of the double-sharpened blades for a one pass even trim.

Even trimming results

- Trims evenly and captures low-lying hairs
- Self-sharpening metal blades are precise even without oiling
- Click-on precision trimmer for perfect edges and details

Precise styling

- 40 lock-in length settings from 0.4- 20mm
- Customizable precision steps for every beard style

Easy to use

- Quickly see the status of your trimmer's battery
- 90 min runtime after a 1 hour charge, or plug it in
- 100% waterproof for easy, thorough cleaning
- Warranty for purchase protection

Highlights

Lift & Trim PRO system



Stubble doesn't stand a chance. The Lift&Trim Pro system captures all your low-lying hairs and lifts them up toward the blades for a precise cut – whilst still being an ideal trimmer for long beards too.

Self-sharpening metal blades



The stainless steel blades are double-sharpened, cutting even the thickest hair precisely. They sharpen themselves by lightly brushing against each other, so no replacement or oiling is needed throughout your trimmer's lifetime.

40 lock-in length settings



Adjust your combs with the zoom wheel to your preferred trimming length and achieve the beard style you want. Use the short beard comb for 0.4–10 mm lengths settings or the long beard comb from 10–20 mm.

Customizable precision



0.2mm steps between 0.4–2mm for a precise short beard style; 0.5mm steps between 2–5mm to achieve an even 3-day beard; 1mm steps above 5mm for long beard maintenance.

Precision trimmer



Trim your moustache or define details and edges in hard to reach areas with the click-on precision trimmer.

90 min Li-ion power



The advanced Li-ion battery provides 90 minutes of powerful, cordless use after 1 hour charge. You can also use your trimmer plugged in or the quick-charge function gives you one full trim after just 5 minutes of charging.

100% waterproof



Simply rinse your waterproof beard trimmer under the tap to thoroughly clean it.

Battery indicator



The battery indicator shows when your trimmer's battery is empty, charging, or full.

Built to last



All of our grooming products are built to last. They come with a 2 year warranty and they never need to be oiled.

Specifications

Cutting system

Cutting element: Stainless steel blades

Range of length settings: 0.4- 20mm

Precision (size of steps): From 0.2mm

Number of length settings: 40

Ease of use

Zoom wheel: Easily adjust length settings

Display: Battery indicator

Operation: Corded & Cordless use

Cleaning: Fully washable

Power

Battery Type: Lithium-ion

Run time: 90 minutes

Charging: 1 hour full charge, 5 min quick charge

Automatic voltage: 100-240 V

Service

2-year warranty

No oil needed

Accessories

Comb: Lift & Trim comb, Long beard comb

Detail trimmer included

Stand: Charging stand

Pouch: Luxurious pouch

