

PHILIPS

Beard trimmer

Beardtrimmer series
5000

0.2mm precision settings

Self-sharpening metal blades

90 min cordless use/1h charge

Lift & Trim PRO system



BT5515/15



One pass even trim

2x more precision with Lift & Trim PRO system

The even and precise trim you want when creating your 3-day stubble, short or long beard look. Our innovative Lift & Trim PRO system lifts the hairs up to the level of the double-sharpened blades for a one pass even trim.

Even trimming results

- Guides low-lying hairs towards the blades for an even trim
- Self-sharpening metal blades are precise even without oiling
- Click-on precision trimmer for perfect edges and details

Precise styling

- 40 lock-in length settings from 0.4- 20mm
- Customizable precision steps for every beard style

Easy to use

- Quickly see the status of your trimmer's battery
- 90 min runtime after a 1 hour charge, or plug it in
- 100% waterproof for easy, thorough cleaning
- 2 year warranty, worldwide voltage, no oil needed

Highlights

Lift & Trim PRO system



Trim your stubble in one stroke with our innovative Lift & Trim PRO system. It lifts low-lying hairs and guides them towards the sharp metal blades for a precise cut.

Self-sharpening metal blades



The stainless steel blades are double-sharpened, cutting even the thickest hair precisely. They sharpen themselves by lightly brushing against each other, so no replacement or oiling is needed throughout your trimmer's lifetime.

40 lock-in length settings




Adjust your combs with the zoom wheel to your preferred trimming length and achieve the beard style you want. Use the short beard comb for 0.4–10 mm lengths settings or the long beard comb from 10–20 mm.

Customizable precision



0.2mm steps between 0.4–2mm for a precise short beard style; 0.5mm steps between 2–5mm to achieve an even 3-day beard; 1mm steps above 5mm for long beard maintenance.

Precision trimmer



Trim your moustache or define details and edges in hard to reach areas with the click-on precision trimmer.

90 min Li-ion power



The advanced Li-ion battery provides 90 minutes of powerful, cordless use after 1 hour charge. You can also use your trimmer plugged in or the quick-charge function gives you one full trim after just 5 minutes of charging.

100% waterproof



Simply rinse your waterproof beard trimmer under the tap to thoroughly clean it.

Battery indicator



The battery indicator shows when your trimmer's battery is empty, charging, or full.

Built to last



All of our grooming products are built to last. They come with a 2 year worldwide warranty, worldwide voltage compatibility, and they never need to be oiled.

Specifications

Cutting system

Cutting element: Stainless steel blades
Range of length settings: 0.4- 20mm
Precision (size of steps): From 0.2mm
Number of length settings: 40

Ease of use

Zoom wheel: Easily adjust length settings
Display: Battery indicator
Operation: Corded & Cordless use
Cleaning: Fully washable

Power

Battery Type: Lithium-ion
Run time: 90 minutes
Charging: 1 hour full charge, 5 min quick charge
Automatic voltage: 100-240 V

Service

2-year warranty
No oil needed

Accessories

Comb: Lift & Trim comb, Long beard comb
Detail trimmer included
Stand: Charging stand
Pouch: Luxurious pouch

