

PHILIPS

Vacuum Beard Trimmer

Beardtrimmer series 7000

0.5mm precision settings

Full metal blades

60 min cordless use/1h charge

Captures up to 90% cut hair*



BT7201/15



Less mess vacuum trimmer

Integrated vacuum captures up to 90% cut hair*

Trim your beard, mustache and sideburns while keeping tidy with this trimmer. Its powerful vacuum catches cut hair as you go along, giving you a mess-free trim.

Vacuum system

- Guaranteed less mess with integrated vacuum

Even trimming results

- Lifts and guides hairs for an effortless even trim
- Double-sharpened stainless steel blades for faster trimming
- Precision trimmer for finishing up in hard to reach areas

Easy to use

- Adjusts to different length settings
- 60 minutes run time after a 1-hour charge or plug it in
- Lights indicate when battery is low, empty, full or charging
- Simple maintenance
- 2 year guarantee, worldwide voltage and no need to oil



reddot award 2016
winner



asimpleswitch.com



Highlights

Integrated vacuum system



Trim your beard, mustache and sideburns while keeping tidy with this trimmer. Its powerful vacuum catches cut hair as you go along, giving you a mess-free trim.

Innovative lift & trim system



Trim your stubble in one quick stroke. Our innovative lift & trim system raises each hair, then guides it toward the double-sharpened stainless steel blades. The result is an even stubble or trim in just one go.

Double-sharpened blades



Strong steel blades are double-sharpened and made to last a very long time to cut through even thick hair. They sharpen themselves by lightly brushing against each other as you trim.

20 lock-in length settings



Cut to the exact length you're after. Just spin the precision dial to one of 20 length settings between 0,5 - 10mm in 0.5mm increments.

Corded and cordless use



Charge your beard trimmer for 1 hour to get 60 minutes of cordless use. If you need more energy while trimming, you can simply plug the trimmer into the wall. This trimmer has been designed to run both cordless and plugged in.

Battery indicators



The battery indicators in this trimmer let you know what your battery status is: Low, empty, charging or full. This way, you can charge your trimmer on time and fully, so you won't end up with an empty battery in the middle of your trim.

Precision trimming



When you are done trimming, just click on this precision trimmer to finish up your style with defining details and edges or trimming your moustache.



reddot award 2016
winner

Red Dot Award 2016: Winner

Beardtrimmer series 7000Red Dot Award 2016: Winner



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.



iF DESIGN AWARD 2017

Beardtrimmer series 7000iF DESIGN AWARD 2017

Specifications

Cutting system

Precision (size of steps): By 0.5 mm

Range of length settings: 0.5 up to 10 mm

Cutting element: Stainless steel blades

Create the look you want

Number of length settings: 20 integrated length settings

Accessories

Precision trimmer

Maintenance: Cleaning brush

Ease of use

Zoom wheel: Easily adjust length settings

Display: Battery light

Cleaning: Rinseable attachments

Operation: Corded & Cordless use

Design

Color: Black

Power

Run time: 60 minutes

Battery Type: NiMH

Charging: 1 hour full charge

Automatic voltage: 100-240 V

Service

2-year guarantee

No oil needed

