

# PHILIPS

## Vacuum Beard Trimmer

### Beardtrimmer series 7000

0.5mm precision settings

Full metal blades

60 min cordless use/1h charge

Captures up to 90% cut hair\*



BT7201/15



## Less mess vacuum trimmer

Integrated vacuum captures up to 90% cut hair\*

Trim your beard, mustache and sideburns while keeping tidy with this trimmer. Its powerful vacuum catches cut hair as you go along, giving you a mess-free trim.

#### Vacuum system

- Guaranteed less mess with integrated vacuum

#### Even trimming results

- Lifts and guides hairs for an effortless even trim
- Double-sharpened stainless steel blades for faster trimming
- Precision trimmer for finishing up in hard to reach areas

#### Easy to use

- 20 lock-in length settings, 0,5 - 10mm with 0,5mm precision
- 60 minutes run time after a 1-hour charge or plug it in
- Quickly see the status of your trimmer's battery
- Just empty the chamber and rinse the blades under water
- 2 year guarantee, worldwide voltage and no need to oil



reddot award 2016  
winner



asimpleswitch.com



# Highlights

## Integrated vacuum system



Trim your beard, mustache and sideburns while keeping tidy with this trimmer. Its powerful vacuum catches cut hair as you go along, giving you a mess-free trim.

## Innovative lift & trim system



Trim your stubble in one quick stroke. Our innovative lift & trim system raises each hair, then guides it toward the double-sharpened stainless steel blades. The result is an even stubble or trim in just one go.

## Double-sharpened blades



Strong steel blades are double-sharpened and made to last a very long time to cut through even thick hair. They sharpen themselves by lightly brushing against each other as you trim.

## 20 lock-in length settings



Select your preferred trim length by simply turning the zoom wheel on the handle until the length you want is displayed from 0,5 - 10mm with 0,5mm precision. Your chosen length is now "locked in" for a perfectly even trim.

## Corded and cordless use



Charge your beard trimmer for 1 hour to get 60 minutes of cordless use. If you need more energy while trimming, you can simply plug the trimmer into the wall. This trimmer has been designed to run both cordless and plugged in.

## Battery indicator



The battery indicator shows when your trimmer's battery is empty, charging, or full.

## Precision trimming



When you are done trimming, just click on this precision trimmer to finish up your style with defining details and edges or trimming your moustache.



reddot award 2016  
winner

## Red Dot Award 2016: Winner

Beardtrimmer series 7000Red Dot Award 2016: Winner



asimpleswitch.com

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.



## iF DESIGN AWARD 2017

Beardtrimmer series 7000iF DESIGN AWARD 2017

# Specifications

## Cutting system

**Precision (size of steps):** By 0.5 mm

**Range of length settings:** 0.5 up to 10 mm

**Cutting element:** Stainless steel blades

## Create the look you want

**Number of length settings:** 20 integrated length settings

## Accessories

**Precision trimmer**

**Maintenance:** Cleaning brush

## Ease of use

**Zoom wheel:** Easily adjust length settings

**Display:** Battery light

**Cleaning:** Rinseable attachments

**Operation:** Corded & Cordless use

## Design

**Color:** Black

## Power

**Run time:** 60 minutes

**Battery Type:** NiMH

**Charging:** 1 hour full charge

**Automatic voltage:** 100-240 V

## Service

**2-year guarantee**

**No oil needed**

