

PHILIPS

Vacuum Beard Trimmer

Beardtrimmer series 7000

0.5-mm precision settings

Full Metal Trimmer

60 min cordless use/1 hr charge

Captures up to 90% of cut hair*



BT7202/13



Less mess vacuum trimmer

Integrated vacuum captures up to 90% of cut hair*

Trim your beard, moustache and sideburns while keeping tidy with this trimmer. Its powerful vacuum catches cut hair as you go along, giving you a mess-free trim.

Vacuum system

- Guaranteed less mess with integrated vacuum

Even trimming results

- Lifts and guides hairs for an effortless even trim
- Double-sharpened stainless steel blades for faster trimming
- Precision trimmer for finishing up in hard-to-reach areas

Easy to use

- 20 lock-in length settings, 0.5 - 10 mm with 0.5-mm precision
- 60 minutes' run time after a 1-hour charge or plug it in
- Just empty the chamber and rinse the blades in water
- Quickly see the status of your trimmer's battery
- 2-year guarantee, worldwide voltage and no need to oil



reddot award 2016
winner



asimpleswitch.com




Highlights

Integrated vacuum system



Trim your beard, moustache and sideburns while keeping tidy with this trimmer. Its powerful vacuum catches cut hair as you go along, giving you a mess-free trim.

Innovative lift-and-trim system



Trim your stubble in one quick stroke. Our innovative lift-and-trim system raises each hair and then guides it towards the double-sharpened stainless steel blades. The result is even stubble or an even trim in just one go.

Double-sharpened blades



Strong steel blades are double-sharpened and made to last a very long time to cut through even thick hair. They sharpen themselves by lightly brushing against each other as you trim.

20 lock-in length settings



Select your preferred trim length by simply turning the zoom wheel on the handle until the length you want is displayed, from 0.5 - 10 mm with 0.5-mm precision. Your chosen length is now "locked in" for a perfectly even trim.

Corded and cordless use



Charge your beard trimmer for 1 hour to get 60 minutes of cordless use. If you need more energy while trimming, you can simply plug the trimmer into the wall. This trimmer has been designed to work both cordlessly and while plugged in.

Battery indicator



The battery indicator shows when your trimmer's battery is empty, charging or full.

Precision trimming



When you have finished trimming, just click on this precision trimmer to finish up your style by defining details and edges or trimming your moustache.



reddot award 2016
winner

Red Dot Award 2016: Winner

Beard trimmer series 7000Red Dot Award 2016: Winner



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas — Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.



iF DESIGN AWARD 2017

Beard trimmer series 7000iF DESIGN AWARD 2017

Specifications

Cutting system

Precision (size of steps): By 0.5 mm

Range of length settings: 0.5 mm up to 10 mm

Cutting element: Stainless steel blades

Create the look you want

Number of length settings: 20 integrated length settings

Accessories

Precision trimmer

Maintenance: Cleaning brush

Ease of use

Zoom wheel: Easily adjust length settings

Display: Battery light

Cleaning: Rinseable attachments

Operation: Corded and Cordless use

Design

Colour: Black

Power

Battery Type: NiMH

Run time: 60 minutes

Charging: 1 hour full charge

Automatic voltage: 100-240 V

Service

2 year guarantee

No oil needed

