

PHILIPS

Vacuum Beard Trimmer

Beardtrimmer series 7000

0.5mm precision settings

Full Metal Trimmer

60 min cordless use/1h charge

Captures up to 90% cut hair*



BT7206/15



Less mess vacuum trimmer

Integrated vacuum captures up to 90% cut hair*

Trim your beard, mustache and sideburns while keeping tidy with this trimmer. Its powerful vacuum catches cut hair as you go along, giving you a mess-free trim.

Vacuum system

- Guaranteed less mess with integrated vacuum

Even trimming results

- Lifts and guides hairs for an effortless even trim
- Double-sharpened stainless steel blades for faster trimming
- Skin-friendly, high-performance blades for the perfect trim

Easy to use

- 20 lock-in length settings, 0,5 - 10mm with 0,5mm precision
- 60 minutes run time after a 1-hour charge or plug it in
- Just empty the chamber and rinse the blades under water
- Quickly see the status of your trimmer's battery
- 2 year guarantee, worldwide voltage and no need to oil



reddot award 2016
winner



Highlights

Integrated vacuum system



Trim your beard, mustache and sideburns while keeping tidy with this trimmer. Its powerful vacuum catches cut hair as you go along, giving you a mess-free trim.

Innovative lift & trim system



Trim your stubble in one quick stroke. Our innovative lift & trim system raises each hair, then guides it toward the double-sharpened stainless steel blades. The result is an even stubble or trim in just one go.

Double-sharpened blades




Strong steel blades are double-sharpened and made to last a very long time to cut through even thick hair. They sharpen themselves by lightly brushing against each other as you trim.

20 lock-in length settings



Select your preferred trim length by simply turning the zoom wheel on the handle until the length you want is displayed from 0,5 - 10mm with 0,5mm precision. Your chosen length is now "locked in" for a perfectly even trim.

Skin-friendly blades



Get a perfect yet protective trim, time after time. The beard trimmer's steel blades lightly brush against one another, sharpening themselves as they trim so they stay extra sharp and effective. They also have rounded tips and combs to help prevent skin irritation.

Corded and cordless use



Charge your beard trimmer for 1 hour to get 60 minutes of cordless use. If you need more energy while trimming, you can simply plug the trimmer into the wall. This trimmer has been designed to run both cordless and plugged in.

Battery indicator



The battery indicator shows when your trimmer's battery is empty, charging, or full.

Easy to clean



Once you are done trimming, simply remove the blades by pulling them up, rinse the blades and comb under the tap, empty the hair chamber and brush away any loose hairs with the added cleaning brush for long-lasting performance.



reddot award 2016
winner

Red Dot Award 2016: Winner

Beardtrimmer series 7000 Red Dot Award 2016: Winner



DESIGN
AWARD
2017

iF DESIGN AWARD 2017

Beardtrimmer series 7000 iF DESIGN AWARD 2017

Specifications

Cutting system

Precision (size of steps): By 0.5 mm

Range of length settings: 0.5 up to 10 mm

Cutting element: Stainless steel blades

Create the look you want

Number of length settings: 20 integrated length settings

Accessories

Maintenance: Cleaning brush

Ease of use

Zoom wheel: Easily adjust length settings

Display: Battery light

Cleaning: Rinseable attachments

Operation: Corded & Cordless use

Design

Color: Black

Power

Run time: 60 minutes

Battery Type: NiMH

Charging: 1 hour full charge

Automatic voltage: 100-240 V

Service

2-year guarantee

No oil needed

