

# PHILIPS

## NORELCO

Vacuum beard trimmer, Series 7000

Beardtrimmer 7200

0.5mm precision settings

Stainless steel blades

80 min cordless use/1h charge

Catches up to 90% cut hair\*



BT7215/49



## Powerful suction, less mess

Integrated vacuum catches up to 90% cut hair\*

Trim your beard, mustache and sideburns while keeping tidy with this trimmer. Its powerful vacuum catches cut hair as you go along, giving you a mess-free trim..

### Vacuum system

- Catches up to 90% of cut hair for less mess\*

### Even trimming results

- Lifts and guides hairs for an effortless even trim
- Double-sharpened stainless steel blades for faster trimming
- Precision trimmer & combs to finish up in hard to reach area

### Easy to use

- Select your lengths from 1/32"-13/32" with the zoom wheel
- 80 minutes runtime after a 1 hour charge, or plug it in
- Lights indicate when battery is low, empty, full or charging
- Simple maintenance
- 5 year warranty offer



reddot award 2016  
winner



# Highlights

## Vacuum system



Trim your beard, mustache and sideburns while keeping tidy with this trimmer. High-velocity motor and fan system creates powerful suction to lift and capture maximum hairs, leaving you with less mess to clean up.

## Even trim, less strokes



Innovative lift & trim technology effectively lifts and guides hairs for a more efficient cut. Rounded contour comb technology is designed to deliver a skin friendly and more even trim.

## Self-sharpening steel blades



The blades are designed to effectively cut each hair perfectly, preventing skin irritation. They are double sharpened to cut more hairs in every pass for faster trimming.

## Built-in 20 length settings



Select your preferred trim length by simply turning the zoom wheel until the length you want is displayed from 0,5 -10mm (1/32"to 13/32") with 0,5mm precision.

## Corded and cordless use



Advanced lithium-ion battery delivers maximum power for high performance cutting. Charge your beard trimmer for 1 hour to get 80 minutes of cordless use. It can also be used while charging.

## Battery indicators



The battery indicators in this trimmer let you know what your battery status is: Low, empty, charging or full. This way, you can charge your trimmer on time and fully, so you won't end up with an empty battery in the middle of your trim.

## Precision trimming



When you are done trimming, just click on this precision trimmer to finish up your style with defining details and edges or trimming your moustache with clicking one of the precision combs (3 or 5mm) on the trimmer.



reddot award 2016  
winner

## Red Dot Award 2016: Winner

Beardtrimmer series 7000Red Dot Award 2016:  
Winner



## iF DESIGN AWARD 2017

Beardtrimmer series 7000iF DESIGN AWARD  
2017

# Specifications

## Cutting system

**Precision (size of steps):** By 0.5 mm

**Range of length settings:** 0.5 up to 10 mm

**Cutting element:** Stainless steel blades

## Create the look you want

**Number of length settings:** 20 integrated length settings

## Accessories

**Precision trimmer**

**Comb:** 3mm precision comb, 5mm precision comb

**Maintenance:** Cleaning brush

## Ease of use

**Zoom wheel:** Easily adjust length settings

**Cleaning:** Rinseable attachments

**Display:** Battery light

**Operation:** Corded & Cordless use

## Design

**Finishing:** Chrome finish

## Power

**Run time:** 80 minutes

**Charging:** 1 hour full charge

**Automatic voltage:** 100-240 V

## Service

**2-year warranty:** Yes, Plus 3-years with registration

**No oil needed**

