

PHILIPS

Vacuum Beard Trimmer

Beardtrimmer series 7000

0.5-mm precision settings

Self-sharpening metal blades

Up to 75 min use/1 hr charge

High-performance vacuum system



BT7500/13



Less mess vacuum trimmer

Philips' No. 1 for tidy trimming

Trim your beard, moustache and sideburns while keeping tidy. The new Philips Vacuum Trimmer has an improved, high-performance system with 50% stronger* airflow. It captures cut hair effectively, giving you a mess-free trim.

Less mess vacuum trimmer

- Optimised airflow for a mess-free trim

Even trimming results

- Trims evenly and captures low-lying hairs
- Self-sharpening metal blades are precise even without oiling
- Click-on precision trimmer for perfect edges and details

Easy to use

- 20 lock-in length settings, 0.5 - 10 mm with 0.5-mm precision
- Just empty the chamber and rinse the blades in water
- Quickly see the status of your trimmer's battery
- Up to 75 min runtime after a 1 hour charge, or plug it in
- Warranty for purchase protection

Highlights

High-performance vacuum system



The new Philips Vacuum Trimmer comes with 50% stronger, improved airflow*. The powerful vacuum captures up to 94% of cut hair**, giving you a mess-free trim.

Lift & Trim PRO system



Stubble doesn't stand a chance. The Lift & Trim Pro system captures all your low-lying hairs and lifts them up towards the blades for a precise cut – whilst still being an ideal trimmer for long beards too.

Self-sharpening metal blades



The stainless steel blades are double-sharpened, cutting even the thickest hair precisely. They sharpen themselves by lightly brushing against each other, so no replacement or oiling is needed throughout your trimmer's lifetime.

20 lock-in length settings



Select your preferred trim length by simply turning the zoom wheel on the handle until the length you want is displayed, from 0.5 - 10 mm with 0.5-mm precision. Your chosen length is now "locked in" for a perfectly even trim.

Precision trimmer



Trim your moustache or define details and edges in hard-to-reach areas with the click-on precision trimmer.

75 min corded/cordless use



Charge your beard trimmer for 1 hour to get up to 75 minutes of cordless use or simply use it plugged into the wall. Otherwise, the quick charge function gives you a full trim after just 5 minutes of charging.

Battery indicator



The battery indicator shows when your trimmer's battery is empty, charging or full.

Easy to clean



Once you have finished trimming, simply remove the blades by pulling them up, rinse the blades and comb under the tap, empty the hair chamber and brush away any loose hairs with the added cleaning brush for long-lasting performance.

Built to last



All of our grooming products are built to last. They come with a 2 year warranty and they never need to be oiled.

Specifications

Cutting system

Cutting element: Stainless steel blades

Range of length settings: 0.5 mm up to 10 mm

Precision (size of steps): By 0.5 mm

Create the look you want

Number of length settings: 20 integrated length settings

Power system

5-min quick charge

Ease of use

Zoom wheel: Easily adjust length settings

Display: Battery level indicator

Operation: Corded and Cordless use

Cleaning: Rinseable blades and guards

Power

Run time: Up to 75 minutes

Charging: 1 hour full charge

Battery Type: NiMH

Automatic voltage: 100-240 V

Design

Colour: Black

Finishing: Soft touch

Service

2 year warranty

Accessories

Precision trimmer

Comb: Lift & Trim system

Maintenance: Cleaning brush

