

# PHILIPS

waterproof beard  
trimmer

Beardtrimmer series  
9000

0.2mm precision settings  
Full metal dual-sided trimmer  
60mins cordless use/1h charge  
with laser guide



BT9280/15



## Ultimate precision

The only beard trimmer with a laser guide

Experience superb control on contours with the exclusive laser guide. It allows you to create the precise and symmetric style you want with confidence.

### Precision

- Use the unique laser guide for precise, symmetric results
- The zoom wheel 'locks in' your chosen length setting
- Dual-sided trimmer: 32mm and 15mm sides for perfect details
- The 0.4mm stubble setting gives you a 3-day beard every day

### Skin-friendly performance

- Skin-friendly, high-performance blades for the perfect trim


### Easy to use

- 100% waterproof for easy cleaning
- Detail comb for precision, and beard comb for control
- The LED display clearly shows your chosen length setting
- LED display shows the battery level
- 2-year guarantee, worldwide voltage, no oil needed
- Protective pouch for travel and storage
- 60 minutes cordless use after a 1-hour charge, or plug it in



# Highlights

## World's first laser guide



The unique laser guidance system projects a sharp line of light to pre-align your style before you trim. It will point out where the hairs will be cut so you get it right every time.

## Dual-Sided trimmer



Take off the adjustable length comb, and there's a reversible, dual-sided precision trimmer underneath. One side is a 32mm high-performance trimmer. Turn it around, and there's a 15mm-wide precision trimmer – perfect for getting into small spaces, like under your nose or around your mouth. It's designed to cut very close while still protecting your skin, and its small size and angled design make it easy to see what you are doing for fine lines and details.

## 17 lock-in length settings



To select your preferred trim length, just turn the zoom wheel on the handle until the length you want is displayed. Your chosen length is now 'locked in' for a precise and even trim.

## Skin-friendly high performance



The steel blades lightly brush against each other, so they sharpen themselves as you trim! The blades stay extra-sharp to always cut hairs neatly and effectively, but have rounded blade tips and combs to prevent skin irritation.

## 100% waterproof



To clean the trimmer head, simply rinse it under the tap.

## Detail and beard combs



The detail comb gives you more precision as you trim. Use it instead of the beard comb to get into tight spots, or to round off the edges of your beard. The beard comb gives you more control for a fast and even trim.

## LED display



The LED display shows your chosen length setting in millimeters, so you're always in control of your style.

## LED battery level indicator

The LED display indicates the battery level, so you're never caught short.

## Perfect 3-day beard every day



If you want a perfect 3-day beard, just use the trimmer's shortest setting of 0.4mm. For a perfectly groomed longer beard, simply adjust the setting to the exact length you need.



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO<sub>2</sub> emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

**Accessories**

Beard comb  
Detail Comb  
Maintenance: Cleaning brush

**Ease of use**

Cleaning: 100% Waterproof  
Battery Run time: 1 hour charge 60 mins runtime  
Operation: Corded & Cordless use

**Power**

Automatic voltage: 100-240 V

**Service**

Guarantee: 2 - Year Worldwide Guarantee

**Precision**

Length Settings: 17 Length from 0.4 mm to 7 mm

**Categorization**

Trimmers: BeardTrimmer9000

