

PHILIPS

NORELCO

waterproof beard
trimmer

Beardtrimmer series
9000

0.2mm precision settings
Full metal dual-sided trimmer
60mins cordless use/1h charge
with laser guide



BT9295/41



Ultimate precision

The only beard trimmer with a laser guide

Experience ultimate control with an exclusive laser guide, allowing you to create the exact look you want with total confidence.

Precision

- Use the unique laser guide for precise, symmetric results
- The zoom wheel 'locks in' your chosen length setting
- Dual-sided reversible trimmer for ultimate versatility
- Set length to 1/64" (0.4mm) for perfect stubble every day

Skin-friendly performance

- Skin-friendly, high-performance blades for the perfect trim

Easy to use


- Water-resistant for easy cleaning
- Detail comb for precision, and beard comb for control
- The LED display clearly shows your chosen length setting
- LED display shows the battery level
- 60 minutes cordless use after a 1-hour charge, or plug it in
- 2 year warranty, worldwide voltage and no need to oil



asimpleswitch.com

Highlights

World's first laser guide



The unique laser guidance system projects a sharp line of light to pre-align your style before you trim. It will point out where the hairs will be cut so you get it right every time.

17 lock-in length settings



To select your preferred trim length, just turn the zoom wheel on the handle until the length you want is displayed. Your chosen length is now 'locked in' for a precise and even trim.

Reversible trimmer



The dual-sided reversible trimmer gives you the versatility to create your unique look. On one side, the 1 17/64" (32mm) high-performance trimmer cuts very close while protecting your skin. On the other side, the 5/8" (15mm) precision trimmer creates a detailed look, even in those hard-to-reach areas like under the nose and around the mouth. The trimmer's small size and angled design make it easy to see what you are doing for accurate fine lines and details.

Skin-friendly high performance



The steel blades lightly brush against each other, so they sharpen themselves as you trim! The blades stay extra-sharp to always cut hairs neatly and effectively, but have rounded blade tips and combs to prevent skin irritation.

Water-resistant



To clean, simply rinse the water-resistant trimmer under the tap.

Detail and beard combs



The detail comb gives you more precision as you trim. Use it instead of the beard comb to get into tight spots, or to round off the edges of your beard. The beard comb gives you more control for a fast and even trim.

LED display



The LED display shows your chosen length setting in millimeters, so you're always in control of your style.

LED battery level indicator

The LED display indicates the battery level, so you're never caught short.

Rechargeable and corded use



You get 60 minutes of cordless use after a 1-hour charge. If you run out of battery power while trimming, just plug it in and keep trimming.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Accessories

Beard comb

Detail Comb

Maintenance: Cleaning brush

Pouch

Ease of use

Cleaning: 100% Waterproof

Battery Run time: 1 hour charge 60 mins runtime

Operation: Corded & Cordless use

Precision

Length Settings: 17 Length from 0.4 mm to 7 mm

Power

Automatic voltage: 100-240 V

Service

Guarantee: 2 - Year Worldwide Guarantee

Categorization

Trimmers: BeardTrimmer9000

