

PHILIPS

Laser guided beard
& stubble trimmer

Beardtrimmer series
9000

Follow laser line to get precise
trim

Stainless steel blades

Length settings - 0.4 to 7 mm

Wet & dry use



BT9297/13



World's 1st Laser-Guided Beard Trimmer

Perfect symmetry with laser-guided trimmer

Perfect your beard with our exclusive laser guidance system. Follow the red line of light to get a sharp, symmetrical trim on both sides of your face.

Precision

- Laser guidance for a precise, symmetrical trim every time
- Trim in precise steps of 0.2 mm, from 0.4 mm to 7 mm
- Detail trimmer for perfect edges and details

Cutting performance

- Full metal blades are double-sharpened for faster trimming
- Lifts and guides hairs for an effortless even trim
- Cuts consistently, even through denser hair
- Skin-friendly rounded tips prevent irritation

Battery

- 80 minutes' run time after a 1-hour charge or use plugged in

Easy to use

- LED display clearly shows your length setting
- Quickly see the status of your trimmer's battery
- Easy but thorough cleaning



reddot award 2017
winner

Highlights

Laser guidance



Perfect your beard with our exclusive laser guidance system. Follow the red line of light to get a sharp, symmetrical trim on both sides of your face.

Full metal blades



Our full metal stainless steel blades are extra-strong and double-sharpened. That means they're made to last a very long time, and cut through even the thickest hair. As you trim, they sharpen themselves by lightly brushing against each other. So you get a precise, even cut – time after time.

Innovative lift-and-trim system



Trim your stubble in one quick stroke. Our innovative lift-and-trim system raises each hair and then guides it towards the double-sharpened stainless steel blades. The result is even stubble or an even trim in just one go.

Advanced Li-Ion battery



Our advanced Li-Ion battery allows you to charge your beard trimmer for 1 hour and get 80 minutes of cordless use. If you need more energy while trimming, you can simply plug the trimmer into the wall. This trimmer has been designed to work both cordless and while plugged in.

0.2-mm precision



Style your beard with ultimate accuracy by choosing a hair length down to 0.2-mm precision. Use the zoom wheel to select and lock in the length you want, from 0.4 mm all the way to 7 mm.

LED Display



Turn the zoom wheel to view your chosen length setting in mm on the LED display.

3 level battery indicator



See whether your trimmer is well charged or needs charging – in the blink of an eye. 3 simple bars show you the charge time remaining, as well as the charging status when your trimmer is plugged in.

100% waterproof



The 100% waterproof beard trimmer, simply rinse it under the tap for a thorough, easy clean.



iF DESIGN AWARD 2017

Beard trimmer series 9000iF DESIGN AWARD 2017



reddot award 2017
winner

Red Dot Award 2017: Winner

Beard trimmer series 9000Red Dot Award 2017: Winner

Specifications

Cutting system

Precision (size of steps): From 0.2 mm

Range of length settings: 0.4 up to 7 mm

Cutting element: Stainless steel blades

Non-scratch teeth: For more comfort

Create the look you want

Laser guidance: Perfect symmetric beard

Number of length settings: 17 integrated length settings

Accessories

Comb: Integrated hair lift comb

Detail trimmer included

Pouch: Travel pouch

Power

Battery Type: Lithium-ion

Run time: 80 minutes

Charging: 1 hour full charge

Automatic voltage: 100-240 V

Ease of use

Zoom wheel: Easily adjust length settings

Display: Digital length settings, 3 level battery indicator

Cleaning: Fully washable

Operation: Corded and Cordless use

Design

Finishing: Chrome finish

Service

2 year guarantee

No oil needed

