



#### Laser guided beard & stubble trimmer

- Follow laser line to get precise trim
- Stainless steel blades
- Length settings - 0.4 to 7 mm
- Wet & dry use

BT9297/13

## World's 1st Laser-Guided Beard Trimmer

Perfect symmetry with laser-guided trimmer

Perfect your beard with our exclusive laser guidance system. Follow the red line of light to get a sharp, symmetrical trim on both sides of your face.

### Benefits

#### Precision

- Laser guidance for a precise, symmetrical trim every time
- Trim in precise steps of 0.2 mm, from 0.4 mm to 7 mm
- Detail trimmer for perfect edges and details

#### Cutting performance

- Full metal blades are double-sharpened for faster trimming
- Lifts and guides hairs for an effortless even trim
- Cuts consistently, even through denser hair
- Skin-friendly rounded tips prevent irritation

#### Battery

- 80 minutes' run time after a 1-hour charge or use plugged in

#### Easy to use

- LED display clearly shows your length setting
- Quickly see the status of your trimmer's battery
- 100% waterproof for easy, thorough cleaning

**PHILIPS**

## Features

### Laser guidance



Perfect your beard with our exclusive laser guidance system. Follow the red line of light to get a sharp, symmetrical trim on both sides of your face.

### Full metal blades



Our full metal stainless steel blades are extra-strong and double-sharpened. That means they're made to last a very long time, and cut through even the thickest hair. As you trim, they sharpen themselves by lightly brushing against each other. So you get a precise, even cut – time after time.

### Innovative lift-and-trim system



Trim your stubble in one quick stroke. Our innovative lift-and-trim system raises each hair and then guides it towards the double-sharpened stainless steel blades. The result is even stubble or an even trim in just one go.

### Advanced Li-Ion battery



Our advanced Li-Ion battery allows you to charge your beard trimmer for 1 hour and get 80 minutes of cordless use. If you need more energy while trimming, you can simply plug the trimmer into the wall. This trimmer has been designed to work both cordless and while plugged in.

### 0.2-mm precision



Style your beard with ultimate accuracy by choosing a hair length down to 0.2-mm precision. Use the zoom wheel to select and lock in the length you want, from 0.4 mm all the way to 7 mm.

### LED Display



Turn the zoom wheel to view your chosen length setting in mm on the LED display.

### 3-level battery indicator



See whether your trimmer is well charged or needs charging – in the blink of an eye. 3 simple bars show you the charge time remaining, as well as the charging status when your trimmer is plugged in.

### 100% waterproof



Simply rinse your waterproof beard trimmer under the tap to thoroughly clean it.

### Constant power



This trimmer's powerful motor cuts steadily, regardless of any differences in hair density. So you can trim with consistency, from start to finish.

### Skin-friendly rounded tips



Get a perfect, protective trim. The trimmer's blades have rounded tips to prevent skin irritation – even if you don't use a comb.

## Beardtrimmer series 9000

### Detail trimmer



Put the finishing touches to your style. Click on the detail trimmer to define the edges and details of your beard or moustache.

## Specifications

Please note that this is a pre-sales leaflet. The contents of this leaflet reflect the best of our knowledge per date and country mentioned above. The contents of this leaflet are subject to change without notice. Philips does not accept any liability as to the contents of this leaflet.

### Cutting system

Precision (size of steps)	From 0.2 mm
Range of length settings	0.4 up to 7 mm
Cutting element	Stainless steel blades
Non-scratch teeth	For more comfort

### Create the look you want

Laser guidance	Perfect symmetric beard
Number of length settings	17 integrated length settings

### Accessories

Comb	Integrated hair lift comb
Detail trimmer included	Yes
Pouch	Travel pouch

### Power

Battery Type	Lithium-ion
Run time	80 minutes
Charging	1 hour full charge
Automatic voltage	100-240 V

### Ease of use

Zoom wheel	Easily adjust length settings
Display	Digital length settings 3 level battery indicator
Cleaning Operation	Fully washable Corded and Cordless use

### Design

Finishing	Chrome finish
-----------	---------------

### Service

2 year guarantee	Yes
No oil needed	Yes

### Packaging dimensions

Height	24.40 cm
Width	14.00 cm
Depth	6.90 cm
Net weight	0.28 kg
Gross weight	0.43 kg
EAN	08710103809128
Number of products included	1
Country of origin	CN
Harmonised Systems Code	851020

### Outer Carton

Length	28.90 cm
Width	14.90 cm
Height	26.70 cm
Gross weight	1.98 kg
EAN	18710103809125
Number of consumer packages	4



data subject to change  
2019, June 2

Version: 3.0.1  
EAN: 08710103809128

© 2019 Koninklijke Philips N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

[www.philips.com](http://www.philips.com)