

**PHILIPS**

BT9810
















[www.philips.com/support](http://www.philips.com/support)





5.4-10 mm















mm		
0.4	0.6	0.8
1	1.2	1.4
1.6	1.8	2
2.5	3	3.5
4	4.5	5







mm		
5.4	5.6	5.8
6	6.2	6.4
6.6	6.8	7
7.5	8.0	8.5
9	9.5	10





mm		
0.4	0.6	0.8
1	1.2	1.4
1.6	1.8	2
2.5	3	3.5
4	4.5	5































mm		
5.4	5.6	5.8
6	6.2	6.4
6.6	6.8	7
7.5	8.0	8.5
9	9.5	10











— |

| —

— |

| —

— |

| —

— |

| —

© 2019 Koninklijke Philips N.V.  
All rights reserved  
4222.002.9174.2 (14/11/2019)

**EAC**



>75 % recycled paper  
>75 % papier recyclé