

# PHILIPS

## NORELCO

Beard trimmer

Beard trimmer  
9000 Prestige

SteelPrecision Technology

PowerAdapt Sensor

3-level battery indicator



BT9810/40



## Ultimate steel precision for the perfect beard Philips Norelco's best

The Philips Norelco BT9000 Prestige delivers unmatched precision thanks to the built-in metal comb, giving consistent trimming results no matter how much pressure applied.

### **The most precise trim\***

- Ultimate precision and even results
- Glides over the skin for a smooth trim
- Sharp metal blades cut precisely without pulling
- Trimmed to your length, every time

### **Consistent and efficient cutting performance**

- Tackle dense, bushy and long beards for a precise, even trim
- Up to 120 min runtime after a 1 hour charge

### **Premium experience**

- High quality build for long performance
- Easy to clean
- See remaining battery life at a glance
- Store and go

# Highlights

## SteelPrecision Technology



Create the style of beard that you want with a precise and even finish with Philips 9000 Prestige Beard trimmer for men. Thanks to the metal comb and strong cutter that is integrated into the build, this system does not bend like a plastic comb, no matter the pressure. This helps our precision beard trimmer to always deliver the most even and precise trimming results\*.

## Anti-friction skin follower



Get the most even result from your trim. This beard trimmer for men always follows the contours of your face, with an anti-friction coating that allows it to effortlessly and comfortably glide over your skin.

## Full metal blades



Philips beard trimmer 9000 Prestige cuts even the thickest hair without pulling, so you stay comfortable while you trim. And because the blades are full metal, they stay sharp for life.

## 0.2 mm precision



Trim your beard, so you control how long you want it. Simply flick the zoom wheel of your Philips trimmer to one of 30 length settings from 0.4 to 10mm

## PowerAdapt Sensor



Get a consistent trim no matter how thick or long your beard is. The steel beard trimmer checks hair density 125 times per second and auto-adjusts to maintain constant power.

## Up to 120 min Li-Ion power



Don't be tangled up in cords while using your beard trimmer – our trimmer operates for up to 120 minutes on a single 1-hour charge, or gives one full trim on a quick 5-min charge.

## Lasting steel body



Philips 9000 Prestige is built to last. It's made of high-quality stainless steel for a timeless high-end look.

## 3-level battery indicator



You can clearly see how much power is left. 3 simple bars show you the remaining power, and when the trimmer is charging.

## 100% waterproof



Simply pop the head open and rinse clean this waterproof beard trimmer under running water.

# Specifications

## Cutting system

**Cutting element:** Full metal blades

**Range of length settings:** 0.4 mm up to 10 mm

**Precision (size of steps):** 0.2 mm

**Number of length settings:** 30

**Cutting technology:** SteelPrecision, skin follower

## Ease of use

**Zoom wheel:** Easily adjust length settings

**Operation:** Corded & Cordless use

**Cleaning:** 100% Waterproof

**Battery indicator:** 3-level indicator

## Power

**Battery Type:** Lithium-ion

**Run time:** 120 minutes

**Charging:** 1 hour full charge, 5 min quick charge

**Automatic voltage:** 100-240 V

## Service

**2-year warranty**

**Usage:** Oil in pack

## Accessories

**Comb:** Click-on Long beard comb

**Premium storage & travel case**

