

PHILIPS

Milk frother

Non-stick coating

Fits 120ml milk

Enough for 2 cappuccinos

Prepares hot & cold froth



CA6502/65



Perfect milk foam for your coffee

Dishwasher proof elements for utmost ease of use

The Philips milk frother creates the best milk foam you can wish for – both hot and cold. The perfect companion for all your coffee recipes, the fully automatic milk frother is extremely easy to use – and clean!

Easy to use

- 360° Base
- One touch for easy operation

Easy to clean

- Dishwasher proof whisker and lid
- Non-stick coating for easy cleaning

For Hot & Cold recipes

- Hot & cold milk frothing for a variety of coffee recipes

Perfect milk foam

- Enough milk foam for 2 Cappuccinos
- Mechanical whisking for ultimate foam fineness


Highlights

Milk foam for 2 Cappuccinos



With a capacity of 120ml the milk foam prepared with the Philips milk frother will be enough to prepare 2 Cappuccinos.

Dishwasher proof parts




The whisker and lid of the Philips milk frother are dishwasher proof for easy cleaning.

For Hot & Cold recipes




The milk frother provides the freedom to create and enjoy a variety of hot and cold coffee recipes at home such as a latte macchiato, cappuccino or the perfect iced coffee.

Mechanical whisking




Set to the ideal temperature and speed, the Philips milk frother and its innovative frothing whisker creates the ultimate in foam stiffness and fineness.

Non-stick coating




Cleaning the Philips milk frother requires only a rinse and a swipe of towel thanks to the non-stick coating and the smooth surface inside out. The waterproof casing allows washing the milk frother with ease.

360° Base



The cordless 360 degrees pirouette base of your Philips milk frother makes for easy lifting and placing.

One touch for easy operation



The Philips milk frother offers one touch button for easy operation.

Specifications

Design

Color: Black

Finishing

Material of main body: Stainless steel & plastic

Country of origin

Made in: China

Service

2-year worldwide guarantee

Technical specifications

Cord length: 0.75 m

Frequency: 50 Hz

Voltage: 220-240 V

Capacity milk carafe: 120 L

Frothing time: 130 sec

Weight and dimensions

Dimensions of packaging (WxDxH): 151 x 151 x 217 mm

Dimensions of product (WxDxH): 130 x 130 x 200 mm

Weight of product: 0.76 kg

