

Saeco AquaClean Calc and Water filter

- For Espresso machines
- No descaling up to 5000 cups*
- Improves coffee taste



CA6903/47

No descaling guaranteed for up to 5000 cups*

With each filter you can enjoy up to 625 cups*!

With Saeco's patented AquaClean water filter you don't have to descale your espresso machine for up to 5000 cups*.

Forget about descaling for up to 5000 cups*

- Naturally removes calcium thanks to ion-exchange technology
- Your machine will not clog thanks to the micro-porous filter

Pure water delivers the purest coffee

- Clear water optimally purified by the patented water flow
- Micro-porous filter blocks any impurities


Easy to install and use

- Effortlessly activate the filter with the click&go system
- Activating AquaClean deactivates the descaling alarm

PHILIPS

Saeco, a Philips brand

 **Saeco**



Highlights

Clear water optimally purified



Thanks to the patented flow, the water inside the water filter takes a longer path before entering your super-automatic coffee machine. This ensures a deeper purification for clear water and fine tasting coffee.

Click&Go system




Such an enduring feature could not be quicker to install. Just plug your AquaClean filter in the water tank of your Saeco super-automatic espresso machine, activate it via the user interface, and you are ready to enjoy up to 5000 pure coffee cups without descaling*. It's not until after 8 filter replacements that the machine will reactivate the descaling process alarm. Machines equipped with AquaClean have a sticker on the water tank.

Descaling alarm deactivatedAct



The AquaClean ensures only pure and filtered water flows into your Full Automatic coffee machine, so the descaling alarm is automatically deactivated. Endless, hassle-free coffee of the finest quality is yours to enjoy - and it's not until after 8 filter replacements that the machine will reactivate the descaling process alarm. Machines equipped with AquaClean have a sticker on the water tank.

Ion-exchange Technology



The ion-exchange technology removes calcium from the water before entering your coffee machine, thus preventing its formation. If the filter is replaced timely at machine request, you can enjoy up to 625 cups with each filter*

Micro-porous filter



Ridding your brew of any small particles makes a huge difference to your in-cup quality. The micro-porous filter prevents impurities from contaminating the water, so every cup you make will be fresh, clean and delicious.

Micro-porous filter



Ridding your brew of any small particles makes a huge difference to your in cup quality. The micro-porous filter prevents impurities from contaminating the water, so you can guarantee every cup you make will be fresh, clean and delicious.

Calc and Water filter

For Espresso machines No descaling up to 5000 cups*, Improves coffee taste

CA6903/47

Specifications

Technical specifications

- Country of origin: Switzerland
- Material of the main body: Plastic

Service

- 1-year guarantee

Issue date 2019-03-24

© 2019 Koninklijke Philips N.V.
All Rights reserved.

Version: 2.0.1

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

EAN: 00 07502 00605 32

www.philips.com

* Based on 8 filters replacement as indicated by the machine. Actual number of cups depends on selected coffee varieties, rinsing and cleaning patterns.
* Actual number of cups depends on selected coffee varieties, rinsing and cleaning patterns