



Calc and Water filter

- For Espresso machines
- No descaling up to 5000 cups*
- Improves coffee taste

CA6903/47

No descaling guaranteed for up to 5000 cups*

With each filter you can enjoy up to 625 cups*!

With Saeco's patented AquaClean water filter you don't have to descale your espresso machine for up to 5000 cups*.

Benefits

Forget about descaling for up to 5000 cups*

- Naturally removes calcium thanks to ion-exchange technology
- Your machine will not clog thanks to the micro-porous filter

Pure water delivers the purest coffee

- Clear water optimally purified by the patented water flow
- Micro-porous filter blocks any impurities

Easy to install and use

- Effortlessly activate the filter with the click&go system
- Activating AquaClean deactivates the descaling alarm

PHILIPS

AquaClean

Features

Clear water optimally purified



Thanks to the patented flow, the water inside the water filter takes a longer path before entering your super-automatic coffee machine. This ensures a deeper purification for clear water and fine tasting coffee.

Click&Go system



Such an enduring feature could not be quicker to install. Just plug your AquaClean filter in the water tank of your Saeco super-automatic espresso machine, activate it via the user interface, and you are ready to enjoy up to 5000 pure coffee cups without descaling*. It's not until after 8 filter replacements that the machine will reactivate the descaling process alarm. Machines equipped with AquaClean have a sticker on the water tank.


Descaling alarm deactivated



The AquaClean ensures only pure and filtered water flows into your Full Automatic coffee machine, so the descaling alarm is automatically deactivated. Endless, hassle-free coffee of the finest quality is yours to enjoy - and it's not until after 8 filter replacements that the machine will reactivate the descaling

process alarm. Machines equipped with AquaClean have a sticker on the water tank.

Ion-exchange Technology



The ion-exchange technology removes calcium from the water before entering your coffee machine, thus preventing its formation. If the filter is replaced timely at machine request, you can enjoy up to 625 cups with each filter*

Micro-porous filter



Ridding your brew of any small particles makes a huge difference to your in-cup quality. The micro-porous filter prevents impurities from contaminating the water, so every cup you make will be fresh, clean and delicious.

Micro-porous filter



Ridding your brew of any small particles makes a huge difference to your in-cup quality. The micro-porous filter prevents impurities from contaminating the water, so you can guarantee every cup you make will be fresh, clean and delicious.

Specifications

Please note that this is a pre-sales leaflet. The contents of this leaflet reflect the best of our knowledge per date and country mentioned above. The contents of this leaflet are subject to change without notice. Philips does not accept any liability as to the contents of this leaflet.

Technical specifications

Country of origin	Switzerland
Material of the main body	Plastic

Service

1-year guarantee	Yes
------------------	-----

* Based on 8 filters replacement as indicated by the machine. Actual number of cups depends on selected coffee varieties, rinsing and cleaning patterns.

* Actual number of cups depends on selected coffee varieties, rinsing and cleaning patterns



data subject to change
2019, March 23
Version: 2.0.1
UPC: 00075020060532

© 2019 Koninklijke Philips N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

www.philips.com