



Philips

Complete milk carafe

- PHILIPS 4000
- Black
- PHILIPS 3100 / INCANTO
- GranBaristo

CP0153

Complete carafe kit

Please check specifications for compatible product

Carafe to be used with espresso machines. The transparent material makes it easy to control the milk level. Order an extra jug here — when one needs to be cleaned, you can use the other!

Benefits

Ease of using Philips spare parts

- Easily renew your product with original Philips parts

Features

Easy replacement of product parts

From time to time your product needs a facelift, and with Philips consumer replacement parts to renew your product, it's never been so easy! All this with guaranteed Philips quality.

Specifications

Please note that this is a pre-sales leaflet. The contents of this leaflet reflect the best of our knowledge per date and country mentioned above. The contents of this leaflet are subject to change without notice. Philips does not accept any liability as to the contents of this leaflet.

Replaceable part

Fits product types: HD8847

HD8834
HD8917

PHILIPS

Fits product type HD8964
HD8965

Suitable for:

GranBaristo series HD8966/11
HD8967/01
HD8968/01



data subject to change
2016, November 18

Version: 5.2.1
EAN:

© 2016 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com