

PHILIPS

Sealing ring I

Black

CP6689



Blending reinvented – with vacuum

Check the specifications for compatibility

Vacuum blending prevents oxidation during blending and results in a fresher and tastier drink full of vitamins. High-speed blending with 1400 W, 35,000 rpm powerful motor and ProBlend 6 3D technology unlocks millions of nutrients.

Ease of using Philips spare parts

- Easily renew your product with original Philips parts

Highlights

Easy replacement of product parts

From time to time your product needs a facelift, and with Philips consumer replacement parts to renew your product, it's never been so easy! All this with guaranteed Philips quality.

Specifications

Replaceable part

Fits product types:: HR3752, HR3756

Suitable for:

SENSEO® Original: HR3752/00, HR3756/00

