

PHILIPS

Water container

Pearl White

SENSEO® SARISTA

CRP937/01



Water tank for the SENSEO® SARISTA coffee maker Suitable for the Pearl White model (HD8010/10)

This water tank for the Philips SENSEO® SARISTA bean-funnel coffee maker holds 1.25 litre of water, which is enough for six cups of coffee.

Ease of using Philips spare parts

- Easily renew your product with original Philips parts

Highlights

Easy replacement of product parts

From time to time your product needs a facelift, and with Philips consumer replacement parts to renew your product, it's never been so easy! All this with guaranteed Philips quality.

Specifications

Replaceable part

Fits product type:: HD8010/10

