

PHILIPS

Mobile Phone

E518

Black

LTE/WCDMA/TD-SCDMA/CDMA/GSM

CTE518BK



Always in-touch

Featuring a 2.8 inch touch screen and supporting all-mode 4G, Philips E518 delivers you VoLTE talking quality and outstanding user experience. WLAN hotspot, rear and front cameras, all together make communication convenient and enjoyable.

Always on, always connected

- Dual SIM

Designed for you

- Radio Data System for on-screen station text information
- Superb 2070mAh battery
- Access all major 4G/3G/2G bands in China

Capture and share your life

- 2 megapixel digital camera for crisp, vivid pictures

Connect and enjoy

- Excellent surfing experience with Dual 4G (TDD-LTE/FDD-LTE)

Fabulous and practical

- 2.8" TFT display

Highlights

FM Radio with RDS

Commonly used in Europe, RDS text is sent out on the same frequency the radio station broadcasts on. You can choose either the basic RDS display (station name) or subscribe to additional text-based services.

Dual-SIM

The phone supports the use of two SIM cards. This is a useful option that allows you to choose the most convenient rates and save on mobile communication.

2 megapixel camera



Use your 2 megapixel digital camera to enhance your photo experience with crisp, vivid pictures. The intuitive design and user interface allow you to easily take high-resolution photos of up to 1600 x 1200 pixels to use as wallpaper for your phone display; send from your phone via MMS, Bluetooth, or infrared; or print and share.

2070mAh battery

Your Philips mobile phone comes packed with a standout 2070mAh lithium battery for seamless and long lasting connections on the go. With such exceptional battery performance, you can banish nagging worries about missing

important calls from both your professional and personal contacts. And when both work and family matters have been tackled to your satisfaction, you can hone in on transcendent gaming and surfing experiences on a single charge, thanks to the phone's best-in-class power technology.

4G full-band coverage

Allow to access all major 4G/3G/2G bands and modes with superior call reliability and efficiency.

Dual 4G (TDD-LTE and FDD-LTE)

Your Philips mobile phone incorporates dual-mode 4G radio, that allows you to use mobile internet on a blazing speeds both in TDD-LTE and FDD-LTE networks. Now you can enjoy wider LTE coverage with just one phone.

2.8" TFT display

Put the fun and excitement of colorful graphics and photos right at your fingertips with your phone's 2.8" TFT display.

Specifications

Dimensions

Antenna: Integrated
Form Factor: Candy bar
Handset color: Black
Handset dimensions: 133mm x 56.9mm x 14mm
Handset weight: 131g

Network Features

GPRS (Rx+Tx): Class 12, Class B
GSM band: 900, 1800, 1900 MHz
Messaging: SMS (Short Message Service)
EDGE
3G: CDMA2000 EVDO, TD-SCDMA, WCDMA
GSM band(Primary SIM): 1800, 1900, 900 MHz
GSM band(Secondary SIM): 1800, 1900, 900 MHz
WCDMA band: 2100MHz, 900MHz
CDMA band: 800 MHz
4G FDD-LTE: 1800(B3), 2100(B1), 900(B8), 850(B5)
4G TD-LTE: 1900(B39), 2300(B40), 2600(B41), 2100(B34)
TD-SCDMA band: B34, B39
All Mode

Picture/Display

Diagonal screen size (inch): 2.8 inch
Main Display Resolution: 240x320 pixel
Main Display Technology: TFT

Still Picture Playback

Picture Compression Format: BMP, GIF, JPEG, PNG

Video Playback

Compression formats: 3GP

Audio Capturing

Voice recording: Yes, AMR

Audio Playback

Audio supported formats: AMR, MP3, WAV

Audio Recording

Record your own voice

Cameras

Picture resolution: QVGA 320x240

Sound

Ringers: MP3 ringer

Storage Media

Built-in memory (RAM): 512 MB
Memory Card Types: Micro SD
Memory management: Memory status
Maximum memory card capacity: 32 GB
Built-in memory (ROM): 4 GB (Due to memory used by the operating system and pre-installed applications, the actual space available to users may be less than the stated memory capacity.)

Convenience

Buttons and controls: 4-way navigation key and enter, Soft keys
Call Management: Missed Calls, Received Calls
Clock/Version: Digital
Ease of Use: Dedicated Headset plug, Graphical User Interface, Hands free mode, In-flight mode, Keypad Lock, Softkeys, Vibration Alert, Dual SIM cards
Games and applications: Alarm Clock, Calculator, Calendar, Stopwatch, File Manager
Language available: UI: Chinese Simplified, English
Multimedia: FM Radio
Personalisation/Customization: Wallpaper, Ringtones
Vibrator

Multimedia Applications

Memory Card Access: SD card slot

Connectivity

Modem Capabilities: GPRS, SMS, WCDMA, EDGE, HSDPA 42Mbps, HSUPA 11.5Mbps, UL 50Mbps, DL 150Mbps, CSFB, LTE Cat4, VoLTE
Serial connections: USB-MicroUSB data cable
Bluetooth: Yes, Bluetooth V4.2
Headset: Via jack connector

Accessories

Batteries: 2070 mAh (This capacity is the nominal battery capacity. The actual battery capacity for each individual phone may be slightly above or below the nominal battery capacity.)
Standard Package Includes: Battery, Charger, USB data cable, QSG(Quick start guide), Warranty card

Power

Battery Capacity: 2070mAh
Battery Type: Lithium-ion
Standby time: Up to 930.7 hours (theoretical values under ideal conditions, best case)
Talk time: Up to 3.89 hours (theoretical values under ideal conditions, best case)

Green Specifications

Lead-free soldered product
Packaging material: Carton
User manual: Recycled paper

