

# PHILIPS

## Smartphone

S395

Light Blue

FDD-LTE/TDD-LTE/WCDMA/GSM

CTS395BU



## Always in-touch

Philips InTouch Go S395 is your slim on-the-go companion. Crisp images from the high-quality cameras look excellent on a large 18:9 HD+ grand view display. An efficient quad-core processor with impressive battery life never lets you down.

### **Simplicity of use**

- 5.72" 18:9 HD+ IPS touch screen for rich viewing details
- Quality shots with 8 MP AF and 5 MP FF cameras with flash
- 16GB built-in memory and 2GB RAM for excellent experience

### **Designed for you**

- Superlative 3000mAh lithium battery
- Dual SIM

# Highlights

## **5.72" 18:9 HD+ IPS display**

Enjoy seamless and intuitive navigation like never before on your Philips mobile phone's highly responsive 5.72" 18:9 HD+ IPS touch

screen. All it takes is a light touch or a tap to easily zip through photos, browse the web or zoom through menus and applications.

## **Dual-SIM**

The phone supports the use of two SIM cards. This is a useful option that allows you to choose the most convenient rates and save on mobile communication.

# Specifications

## Network Features

**3G:** WCDMA

**GPRS (Rx+Tx):** Class 12, Class B

**GSM band:** 900, 1800 MHz

**Messaging:** Concatenated SMS (Long SMS), E-mail, MMS, Multimedia Message Service, SMS (Short Message Service), SMS multi-target, Predefined SMS

**Services:** OTA provisioning (WAP, MMS), Internet on mobile, WAP 2.0

### EDGE

**4G FDD-LTE:** 2600(B7), 1800(B3), 2100(B1), 800(B20), 900(B8)

**GSM band(Primary SIM):** 1800, 900 MHz

**GSM band(Secondary SIM):** 1800, 900 MHz

**WCDMA band:** 2100MHz, 900MHz

**WiFi:** IEEE 802.11 b,g,n

**4G TD-LTE:** 2600(B38)

## Dimensions

**Antenna:** Integrated

**Form Factor:** Personal Digital Assistant

**Handset dimensions:** 155mm x 73.5mm x 8.35mm

**Handset weight:** Around 152 g (with battery)

**Handset color:** Blue

## Picture/Display

**Main Display Colors:** 16.7M

**Main Display Resolution:** 720x1440 pixel

**Main Display Technology:** TFT IPS

**Diagonal screen size (inch):** 5.72 inch

**Capacitive touchscreen**

## Still Picture Capturing

**Camera:** Integrated

**Flash:** built-in

**Image sensor type:** CMOS

**Preview frame rate:** 30 frames/second

**Picture file format:** JPEG

**Picture resolution:** 8M (3264X2448), 5M (2592x1944)

## Still Picture Playback

**Picture Compression Format:** BMP, GIF, JPEG

**Rotation:** 90 degree steps

**Slide show**

## Video Playback

**Frame rate (fps):** 30

**Resolution (pxl):** 720x1440

## Sound

**Ringers:** MP3 ringer, Polyphonic (64 tones), AMR ringer

## Storage Media

**Built-in memory (RAM):** 2 GB

**Memory Card Types:** Micro SD

**Memory management:** Memory status, Dynamic memory allocation

**Maximum memory card capacity:** 32 GB

**Built-in memory (ROM):** 16 GB

**User Memory:** Available 10.56GB

## Convenience

**Buttons and controls:** Power On/Off, Side keys

**Call Management:** Call Forwarding, Call on Hold, Call Time, Call Waiting\*, Caller ID\*, Emergency Call, Microphone mute, Missed Calls, Multi-party call, Received Calls

**Clock/Version:** Digital, International clock

**Ease of Use:** Graphical User Interface, Hands free mode, Hot Keys, In-flight mode, Vibration Alert, Dual SIM cards, Dedicated Headset plug, Blinking Lights, Screen saver

**Games and applications:** Alarm Clock, Calculator, Calendar, Stopwatch, Countdown timer, Document Viewer, Widget, File Manager, Photo Editor, Flashlight, World clock  
**Language available: UI:** English, Romanian, Russian, Ukrainian

**Personalisation/Customization:**

Downloadable Picture, Downloadable

Ringtones, Wallpaper, Ringtones

**Text input:** Smart predictive input

**Vibrator**

**Volume control**

**Ease of Navigation:** Touch panel

**Multimedia:** FM Radio

**Personal Info Management:** International clock, Smart Phonebook, Task list, Time Zone

## GPS

**Built-in GPS**

**Supports A-GPS**

## Connectivity

**Modem Capabilities:** GPRS, SMS, EDGE, UPL 50Mbps, LTE Cat4, CSFB, DL 150Mbps, LTE, WCDMA, HSDPA 42Mbps, HSUPA 11.5Mbps, VoLTE

**PC Link:** USB 2.0

**Wireless connections:** Bluetooth, Wi-Fi b/n/g 2.4GHz

**Bluetooth profiles:** A2DP, File transfer profile

**Bluetooth version:** 4.2

**Serial connections:** USB-MicroUSB data cable

**Headset:** Via 3.5mm jack connector

## Accessories

**Standard Package Includes:** Battery, Charger, USB data cable, QSG(Quick start guide), Warranty card

## OS

**Android:** Android7.0

## Processor

**1.3 GHz Quad Core Processor**

## Power

**Battery Capacity:** 3000 mAh

**Battery Type:** Polymer battery

**Standby time:** 639 Hours

**Talk time:** 29 Hours

