

Philips  
Xenium

X503  
White

CTX503WHT



## Enduring connection, sleek design

Travel light with the Philips Xenium X503, as its dual SIM card slot and 8 hours talk time save you from carrying two phones or even a charger on a trip. And its sleek design means you don't have to leave your love of style behind either.

### **Always connected**

- Dual SIM for 2 groups of contacts
- Up to 8 hours of talk time

### **Look sharp, stay sharp**

- Slim and compact

### **Multimedia - anytime, anywhere**

- Capture your memories with 3.2 megapixel camera
- Easy tuning with on-screen display on RDS FM radio stations
- Enjoy Bluetooth stereo music
- MicroSD memory card slot for extra memory/ data storage

# PHILIPS

# Highlights

## Dual SIM



Organize your life better and keep your contacts separate by using 2 different phone numbers. With Dual SIM, you don't need to carry 2 phones around.

## Slim and compact

Your Philips mobile phone is designed to set you apart from the crowd. Its slim form factor allows for a handy yet comfortable grip and its

compact size ensures it fits perfectly in our pocket.

## Up to 8 hours talk time



The phone can support up to 8 hours conversation on a single charge.

## Bluetooth stereo music

Your Philips mobile phone supports A2DP Bluetooth Profile. It lets you enjoy your

favorite tunes wirelessly and in high quality stereo music from your Bluetooth headphones.

## MicroSD memory card slot

You can now enjoy extra capacity and storage of multimedia files by inserting a MicroSD memory card into the built-in memory card slot of your phone.

## RDS FM Radio

Enjoy quick and easy tuning to your favorite stations with Radio Data System (RDS) display, which shows the name of the station instead of frequency numbers. RDS also allows stations to transmit text messages and information directly to your radio display, so you can keep updated with news updates and radio promotions.



# Specifications

## Dimensions

- Antenna: Integrated
- Form Factor: Candy bar
- Handset dimensions: 114.5\* 49.5\* 10.95 mm
- Handset weight: 92.8g
- Handset color: White

## Picture/Display

- Diagonal screen size (inch): 2.4 inch
- Main Display Technology: TFT
- Main Display Colors: 262K
- Main Display Resolution: 240x320 pixel

## Network Features

- GSM band: 900, 1800, 1900 MHz
- GPRS (Rx+Tx): Class 12, class B and C
- EDGE
- Voice Codec: FR/EFR/AMR/HR
- Messaging: Concatenated SMS (Long SMS), E-mail, MMS, Multimedia Message Service, SMS CB (Cell Broadcast), SMS (Short Message Service), SMS multi-target, Predefined SMS
- Services: OTA provisioning (WAP, MMS), SIM Toolkit / Release 99, WAP 2.0

## Still Picture Capturing

- Camera: Integrated
- Image sensor type: CMOS
- Picture resolution: VGA (640x480), QVGA (320x240), SXGA (1280x1024), 3M (2048x1536)
- Picture file format: JPEG
- Picture Mode: Night mode, Self-timer mode, Continuous, Normal
- Picture quality: High, Low, Normal
- Special effects preview mode: Normal, Grey scale, Sepia, Blue effect, Green effect, Color invert

## Still Picture Playback

- Picture Compression Format: BMP, GIF, JPEG
- Rotation: 90 degree steps

## Sound

- Ringers: MP3 ringer, Polyphonic (64 tones), Voice memo ringer, AMR ringer
- Equalizer settings: Bass, Classical, Dance, Normal, Party, Pop, Rock, Treble

## Video Capturing

- Video format: MPEG4, 3GP, H.263
- Video mode: Auto, Night
- Video resolution: QCIF

## Video Playback

- Resolution (pxl): 176x144
- Compression formats: 3GP, H.263, MPEG4

## Audio Capturing

- Voice recording: AMR, AWB, WAV

## Audio Playback

- Audio supported formats: ADPCM, AMR, Midi, MP3, AAC, AAC+, WAV, WMA, SP-Midi

## Storage Media

- User memory: 78 MB
- Memory Card Types: Micro SD
- Maximum memory card capacity: 8 GB

## Convenience

- Buttons and controls: 4-way navigation key and enter, Side keys, Soft keys
- Call Management: Call Forwarding, Call on Hold, Call Time, Call Waiting, Conference Call, Emergency Call, Microphone mute, Missed Calls, Multi-party call, Received Calls, Firewall, Caller ID
- Clock/Version: Analogue, Digital, International clock
- Ease of Use: Hands free mode, In-flight mode, Keypad Lock, Hot Keys, Softkeys, Vibra Alert
- Games and applications: Calendar, Alarm Clock, Calculator, Stopwatch, International converter, Currency converter, Lunar Calendar, Java MIDP 2.0, Agenda, Sudoku game
- Language available: UI: English, Chinese Simplified, Chinese Traditional
- Multimedia: FM Radio
- Personal Info Management: Smart Phonebook, Vcard Exchange, Daylight saving, Safeguard, International clock, Time Zone, SD card back-up, Task list
- Personalisation/Customization: Downloadable Animated GIF, Downloadable Java Applications, Downloadable Picture, Downloadable Ringtones, Wallpaper, Ringtones
- Text input: T9
- Vibrator
- Volume control
- Language available: T9 input: English, Chinese Simplified, Chinese Traditional

## Connectivity

- Bluetooth: Bluetooth V2.0
- Bluetooth profiles: A2DP, Handsfree, Headset, File transfer profile
- Headset: Via 3.5mm jack connector
- Modem Capabilities: GPRS
- PC Link: USB 2.0
- Serial connections: USB-miniUSB data cable

## Accessories

- Standard Package Includes: Handset, Battery, Stereo Headset, Charger, USB data cable, User Manual, CD ROM (Mobile Phone Tools)

## Power

- Battery capacity: 1000mAh
- Battery Type: Li-ion
- Battery saving manager: Auto switch on/off
- Standby time: Dual sim up to 600 hours
- Talk time: Up to 8 hours

## Green Specifications

- Lead-free soldered product
- Packaging material: Carton
- User manual: Recycled paper



Issue date 2014-02-12

Version: 3.0.4

12 NC: 8670 000 65782  
EAN: 69 23410 70378 8

© 2014 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)