



Philips 1000 series
Smart video door lock

Remote video intercom
4-inch IPS screen
Realtime's on Wi-Fi connection
Auto locking



DDL111BAFBW

Wonderful life starts from a

With remote video intercom

Philips smart door lock Alpha-VP-5HWS integrates the door viewer, doorbell, and door lock. It adopts a 2MP wide-angle camera and supports Wi-Fi networking, allowing you to view the doorway via the App and bringing a visible security guard.

Smart life locked with excellence

- Always know who's at the door
- Make real-time communication everywhere
- Clearer view of the doorway
- Clearer images even at night
- Instant pushed alert upon abnormal situation

Upgraded smart chip enhances home security

- Allow one-key emergency egress
- Technical lock-picking time exceeds 270 mins
- Protect real password from being peeping
- Instantly protect home security at all times

Easy life doesn't stop here

- Eliminate the hassle of manually locking
- Door's open when the hand is detected
- Say goodbye to the key-only era

PHILIPS

Highlights

Realtime's on Wi-Fi connection




The Philips Alpha-VP-5HWS makes real-time online via the Wi-Fi connection. After binding the Philips EasyKey App, you can view the lock access history, remotely send temporary PIN codes, and view the real-time situation at the door by clicking the video button.

Remote video intercom



When the visitor presses the doorbell, a message will push to the mobile App instantly. You could start the two-way audio by tapping the message box to connect to the App. When the doorbell rings, the video lock will automatically record the video, so you won't miss any visitor information even when you are not home.

4-inch IPS screen



There is a 4-inch IPS display on the indoor escutcheon. You can click the button of the display to view the visitors and the situation at the doorway. Re-clicking the button allows you

to turn off the screen, which is convenient for the elderly and children. Additionally, you can adjust the brightness and sleep mode timeouts of the screen via the mobile APP.

Wide-angle night vision camera



Philips Alpha-VP-5HWS equips with a 144° wide-angle camera and two low-power infrared fill lights. It has daytime mode and night vision mode. When the light is dim, the infrared fill light will automatically turn on, switch to night vision mode, and recognize the facial features within 1 meter from the lock end.

PIR motion detection




Adopted with the PIR sensor, when someone moves around the front door within 3 meters*, the AI humanoid detection algorithm will identify abnormal dynamics by instantly capturing a photo or recording a video. Then it will simultaneously push a message to the APP through the encrypted cloud server, which allows you to fully manage the dynamics at the doorway and avoid security risks.

Emergency unlock rotary knob




The inside escutcheon of the door lock equips a rotary knob. If an emergency leads to the malfunction of the smart door lock, it does not affect the opening of the door lock, and one-key emergency egress could ensure the safety of users.

C-grade lock cylinder



The lock cylinder is the key component that controls the opening of the lock. Adopted multiple anti-theft technologies with a unique design of pin tumbler and vane structure, Alpha-VP-5HWS's C-grade lock cylinder makes the technical lock-picking time exceeds 270 mins*, thus enhanced security is assured.

20-digit hidden PIN code



Featured with the 20-digit hidden PIN code technology, Philips Alpha-VP-5HWS allows you to enter any random number combination for verification and unlock the door as long as there is a consecutive input of the valid password. This feature can effectively prevent peeping and safeguard the real password.

Specifications

Accessory Parts

- Mortise

Design & Appearance

- Color: Obsidian black
- Handle: Push-pull handle

Installation

- Door Thickness: 38-60 mm, 60-90 mm, 90-120 mm, Other range*
- Door Type: Antitheft door, Copper door, Wooden door

Power Specification

- Battery Type: Li-polymer Battery



Issue date 2022-07-15

Version: 1.0.1

12 NC: 8670 001 86842
EAN: 69 71318 50413 6

© 2022 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

* 270 mins data source: Lock cylinder test report.

* 3 meters: the maximum PIR motion detection distance is 3 meters, which can be set to 1 meter, 2 meters and 3 meters via the mobile App.

* Please contact our service agents or authorized dealers for other door range.

* The effect of the digital keypad showed in the photos of this product may be inconsistent with the actual display effect. Please be subject to the digital keypad displaying status under the actual usage scenarios.