

PHILIPS

Push pull smart
door lock

1000 series

Intuitive push-pull use

System wake-up by manual
touch

Auto Locking Function



DDL111LAGSB



Wonderful life starts from Alpha

Full automatic: more safety & freedom

With simplicity brought by speedy unlock and auto lock and safety ensured by dual verification and C-grade lock cylinder, Alpha is a solid choice for a smart life. The ergonomic design even makes it a pleasure to push the door open.

Easy life doesn't stop there

- Enjoy the reassurance after you close the door
- Protect home security at all time
- Intuitive fingerprinting: Unlock swiftly at one go
- Patented full auto mortise: Unlock and open the door at one

Extraordinary design brings outstanding experience

- IML brushed finishing: Smooth and wearable, always like new

Multiple protection in one for overall home safety

- Protect your password security in real time
- Dual verification unlocking: Security is never forgotten
- One-key outside forced lock: Instant alarm upon inside unloc
- Safe handle: No more safety risks, be reassured while away
- C grade lock cylinder: Higher reliability and security

Highlights

Auto locking function



Philips EasyKey Alpha employs full automatic mortise. Without the need for any extra action, the deadbolt will spontaneously pop out after you close the door. If the door is not locked properly, the mortise will give an alarm to remind you of the door lock status.

C grade lock cylinder



Lock cylinder is the key component that controls the opening of the lock and is compared to the heart of a lock. C grade lock cylinder employs multiple anti-theft technologies with unique design of the pin tumbler and vane structure, and is able to give high performance on preventing technical lockpicking.

Dual verification unlocking



In dual verification mode, you can use a combination of any two factors (fingerprint, password and card) as the unlocking solution to ensure doubled security for your home.

Fake PIN code



Philips EasyKey Alpha comes with the feature of Fake PIN Code technology which allows you to enter random number combinations to successfully get identified as long as there is consecutive input of the real password. This feature can effectively prevent peeping and safeguard your real password.

IML brushed finishing



The IML brushed surface has the hardness higher than 2H. Besides, it's waterproof, moisture proof and can keep fingerprint residue out.

Intuitive fingerprinting



The fingerprint sensor is integrated in the push-pull handle so that when you hold the handle, your finger will naturally fall on the sensor. You can simply reach out and intuitively touch the sensor, then push to open after a successful fingerprint verification. The one-step unlocking feature will definitely bring you a fast and convenient door opening experience.

Multiple alarming function



Philips EasyKey Alpha is featured with all-around alarm functions which not only improves the anti-theft level of your home and safeguard you and your family in real time, but also reminds you of the door lock status to create convenience for use.

One-key outside forced lock



Before leaving home, you can touch the outside forced lock key to enable the function. In this mode, opening the door from inside the room will trigger an alarm. This feature can effectively warn you of security risks and upgrade the level of home security.

Patented full auto mortise



The upgraded full automatic mortise makes it possible for instant unlocking right after a successful verification. Once you are recognized, you can directly push or pull the handle to open the door, which greatly simplifies the use of your door lock and brings you a fast and convenient in and out experience.

Specifications

Access Solution

Bluetooth
Card/Key Tag
Fingerprint
Mechanical Key
Password/PIN Code

Accessory Parts

Accessorial Battery: 4 AA alkaline batteries
Certificate
Drilling Template
Installation Accessories
Mechanical Key: 2 keys
Mortise
Mounting Plate
Quick Start Guide
Cleaning Pad
Smart Key Tag: 2 cards
User Manual
Warranty Card

Design & Appearance

Color: Pearl silver
Emergency Escape Design: Indoor fast opening mortise
Ergonomic Design: Push-pull handle design
Fingerprint Sensor: Semiconductor

Handle: Push-pull handle
Main Material: Zinc alloy and aluminium alloy
Surface Processing: Electroplating

Easy Operation

Indicator: Door locks status prompt, Low battery prompt, Mute status prompt, Outside forced lock prompt, System locking prompt
Voice Guide: Human voice guide

Installation

Door Opening Direction: Left inward opening, Left outward opening, Right inward opening, Right outward opening
Door Thickness: 38-60 mm, 60-90 mm, 90-120 mm, Other range*
Door Type: Antitheft door, Copper door, Wooden door
Multi-lock Point: No

Lock Capacity

Card/Key Tag: Up to 100
Fingerprint: Up to 100
Master PIN Code: 1
One-time PIN Code: 1
User PIN Code: Up to 10

Mode

Operating Mode: Auto mode, Manual mode
System Setup Mode: Dual verification mode, Normal mode

Power Specification

Battery Type: Alkaline Batteries
Emergency Power Supply: 5V power bank
Maximum Batteries Capacity: 8 batteries
Power Supply: 4 AA batteries
Time of Use: 10 months*
Working Voltage: 4.5-6V

Smart Lock Functions

Alarm Function: Anti-dismantle alarm, Outside forced lock alarm
Locking Function: Indoor deadlock, System locking
Mortise: Full auto mortise, Hidden C-grade lock cylinder
Safety Function: Dual verification, Fake PIN code, Outside forced lock function, Safe handle function

