

# PHILIPS

Smart rim lock

5000 series

Auto locking function


Support remote controlling

Hidden PIN code

One-time PIN code



DDL151L00GB



## Simple and compact design

### Allow easy installation

Simple design, which is also compact and thin, allows easy installation of different types of doors. Automatic locking, as well as remote controlling, etc. provide you with a better smart life.

#### **Smart life lock with excellence**

- Various ways of unlocking: Say goodbye to the key-only era
- Fully auto mortise: Eliminate the hassle of manually locking

#### **Easy life doesn't stop there**

- One-time PIN code: Convenient for the visitors
- Compact design: Easy installation in different scenario

#### **Intensive protection for home security**

- Hidden PIN code: Protect your password from being peeping

# Highlights

## Various ways of unlocking



Various ways of unlocking



Multiple choices as fingerprint, PIN code, key tag, remote control, and app meet different unlocking needs and allow users to enjoy a smart and convenient door opening experience.

## Fully auto mortise



Fully auto mortise




Philips 5100 employs fully automatic mortise. Without the need for any extra action, the deadbolt will spontaneously pop up after closing the door. If the door is not locked properly, the mortise will give an alert to remind you of the door lock status.

## One-time PIN code



One-time PIN code



When visitors or cleaners come while you are not at home, you can set a one-time password in advance, and it will become invalid after

being used. There is no need to change the master PIN code frequently, which eliminates the hassle of resetting the PIN code(s).

## Compact design



Compact design



The simple and compact design allows easy installation for home, studio, office, etc., which is widely suitable for installation on both inside and outside doors, which could also ensure a private space.

## Hidden PIN code



Hidden PIN code



Featured 32-digit hidden PIN code technology, Philips 5100 allows you to enter any random number combination to get identified and unlock the door as long as there is a consecutive input of the real password. This feature can effectively prevent peeping and safeguard your real password.

## Design & Appearance

Color: Champagne gold

## Installation

Door Thickness: 30-50 mm, Other range\*

## Power Specification

Battery Type: Alkaline Batteries

Time of Use: 8 months\*



\* 8 months: The battery life may be less than 8 months, which is subject to the user's actual unlocking frequency.

\* Other door thickness range: If the thickness of the door is out of the mentioned range, please contact our local dealers or consumer care center.