



Philips
Cordless phone answer
machine

DECT215S

Incredible sound

Enjoy the best sound quality in the most straightforward and easy-to-use phone

Experience best sound quality

- Talk on the phone without holding the handset
- Near to real instrument-sounding ringtones
- CS² Crystal Sound System improves message intelligibility

Benefit from easy-to-use technology

- Plug & Play for fast setting and use of answering machine
- Display indicates the caller's name and number
- Locate your headset by making it ring when paged

PHILIPS

Specifications

Picture/Display

- Diagonal screen size - tele: 4.0 cm
- Effective viewing area: 34 x 20.5 mm
- Lines of text: 1

Sound

- Handset ringers: Instrumental
- Volume Control: digital

Convenience

- Auto out of range warning
- Base Station keys: Paging key
- Battery full indication
- Battery low indication
- Call Management: Call Time, Call Waiting, Caller ID, Conference Call, Explicit Call Transfer
- Drop proof: 120 cm
- Ease of Use: Hands free mode
- Function: Chain dialling, Free handset to handset call
- Handset Keys: Line, Cancel / Recall, Dialling keypad, Loudspeaker, Call log, Phonebook
- Hard Icons: Battery level, In range / Out of range, Line / Internal call, Loudspeaker
- Lines of text: 1
- Multi base capability: 1
- Multi handset capability: 4
- Volume control

Accessories

- AC/DC Adaptor
- Batteries: Ni-MH battery pack
- User Manual

Related Products

- Package contents: Handset, Base, Battery pack NiMH, Telecom Line Cord, Power adapter, User Manual, Warranty leaflet, Sticker

Green Specifications

- Chemical composition: Nickel-Metal Hydride
- Eco Designed
- Halogen-free housing
- Lead-free soldered product
- Packaging material: Carton
- Packaging type: Giftbox

Dimensions

- Base dimensions: 130x85mm
- Base weight: 175g
- Form Factor: Standing on base station
- Handset color: silver
- Handset dimensions: 149mm
- Handset weight: 100g
- Packaging dimensions (W x H x D): 177 x 112 x 182 mm
- Relative humidity (operation): up to 95% at 40°C
- Relative humidity (storage): up to 95% at 40°C
- Temperature range (operation): 0°C to 40°C
- Temperature range (storage): -25°C to 70°C
- Weight incl. Packaging: 0.955 kg

Power

- Ambient temperature: 5 °C to 40 °C
- Battery Type: NiMH
- Charging time: 24 hours hr
- Kind of Battery: Rechargeable
- Power supply: 220-240V
- Radio RF power: <250mW
- Standby time: up to 250 hours
- Talk time: up to 18 hours

Network Features

- Antenna: Fast Selection Technology, Integrated on base, Integrated on handset
- Compatible: GAP
- Dialing: Tone, Pulse

Operator Requirements

- Name and Caller ID
- Caller ID on call waiting
- Operators services phonebook

Answering Machine

- Plug & Play Answering machine
- Recording time capacity: up to 9 min
- Call screening
- Answerphone remote access

Memory Capacity

- Call log entries: 10
- Phonebook: 2 phonebooks of 20 entries

Highlights

Handsfree on Handset

The handsfree speaker phone lets you hold a conversation while your hands are busy with something else and wherever you are. With both the speaker and the microphone in front of the handset, it is just like talking face to face with your correspondent.

Instrumental ringtones

Instead of the traditional aggressive "buzzer" ringtones, instrumental melodies are a more pleasant way to let you know when someone is calling.

CS² Crystal Sound System

Philips' unique Crystal Sound System (CS²) audio technology improves the sound quality of Philips DECT phones. CS² audio quality is demonstrably better than competitive DECT products and brings with it distinct benefits.

Plug & Play answering machine

DECT phones integrate a Plug & Play answering machine which is by default activated with a pre-recorded outgoing message and the answer & record mode for easy setting and use.

Caller name & number display

The name of the person or company calling is shown on the telephone display. The names of first-time callers can be displayed as well as those that are programmed into the telephone beforehand.

Paging key

Instead of looking in every corner of the house, simply call the handset from the base by pressing the dedicated key on the base station and the handset lets you know where it is hiding.



Issue date 2014-02-10

Version: 3.0.5

12 NC: 9961 400 03494
EAN: 87 10895 85595 2

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com