




DLO
TransDock micro

with IntelliTune
For iPod



DLZ97878



Play and charge iPod in the car

plus IntelliTune frequency finder

Enjoy your iPod over your car stereo with this smart little TransDock micro. One-touch IntelliTune finds the ideal frequency for transmitting your iPod over your car's FM radio. Also charges iPod while connected. No installation required!

Convenient access

- 4ft (1.2m) cable for easy access to your device in the car

Enjoy iPod in your car

- FM transmitter broadcasts audio over your car's FM radio
- No installation required

IntelliTune FM frequency finder

- IntelliTune finds open FM frequencies in one click
- 4 programmable FM presets for easy recall

Power on the road

- Charge from 12V outlet

Specifications

Compatibility

- Compatible with: iPod

iPod compatibility

- Compatible with: iPod with docking connector

Power

- Output: 5VDC, 500mA
- Power input: 12VDC, 10W
- Replaceable Fuse

FM Transmitter

- Default Preset Frequencies: 88.1, 94.9, 100.9, 107.9 MHz
- Frequency Adjustment: 0.2 Hz
- Modulation: FM Stereo
- Frequency Range: 88.1 - 107.9

Packaging dimensions

- Packaging type: Blister
- Number of products included: 1
- Packaging dimensions (W x H x D):

- 5.5 x 9.3 x 2.5 inch
- Gross weight: 0.750 lb
- Nett weight: 0.088 lb
- Tare weight: 0.661 lb
- UPC: 8 36258 97878 1

Outer Carton

- Number of consumer packagings: 36
- Outer carton (L x W x H): 24.5 x 22.3 x 13.3 inch
- Gross weight: 30.000 lb
- Nett weight: 3.175 lb
- Tare weight: 26.826 lb
- GTIN: 2 08 36258 97878 5

Inner Carton

- Number of consumer packagings: 6
- Inner carton (L x W x H): 12.0 x 8.0 x 6.5 inch
- Gross weight: 5.000 lb
- Nett weight: 0.529 lb
- Tare weight: 4.471 lb
- GTIN: 1 08 36258 97878 8

Highlights

IntelliTune frequency finder

At the touch of a button, IntelliTune scans the airwaves to find open FM frequencies. You'll know in an instant which station to tune to for broadcasting your device's audio content over the FM radio in your car.

Car FM transmitter

The FM transmitter wirelessly broadcasts the audio content of your device over your car's radio using an open FM frequency, so you can enjoy your music on the road.

No installation required

Quick and easy to use, it requires no custom installation. Simply plug into any 12V auto outlet and you're ready to go, right out of the box.

