



Sound to suit your every need  
PC speakers

**PHILIPS**  
sense and simplicity

## Sound to suit your every need

Enjoy multi-media content from your PC with speakers that are tailored to your every need. The Philips range of PC speakers offers elegant and modern designs that fit comfortably into your home, as well as bold and progressive ones that reflect your gaming experience. Whatever your whim or fancy, you'll find a set that suits your needs. Premium sound quality is not the only thing we promise to deliver in our PC speakers. Expert engineering and design, careful selection of materials and top quality finishing are the first steps we take toward building speakers that offer first-class audio.



## PC speakers with dock for iPod/iPhone




## High fidelity sound

**DS6600 with dock for iPod/iPhone**

Bring life back into your music with deeper & more natural sound delivered through SoundSphere. Dock your iPod/iPhone for playing and charging, or connect directly to PC to enjoy the stunning sound of your multi-media content.



SoundSphere for natural, deeper and wider sound impression



Digital signal processing for digitally equalized sound



Silk dome tweeter for crystal clear sound



Aluminum speakers for high fidelity sound from optimal rigidity



Dock for iPhone/iPad



	DS6600	DS6200	DS6100
Output power RMS	50W	20W	20W
Driver size	4"	3"	2"
With docking	Yes	Yes	Yes
USB powered	-	-	-
Aux-in	Yes	Yes	-
Headphone out	-	-	-

2.0 PC speakers



	SPA8210	SPA7220	SPA3210B	SPA1260	SPA2210	SPA2201	SPA20	SPA5210	SPA2100
Output power RMS	40W	20W	5W	3W	2W	2W	2W	2W	2W
Driver size	3"	2.75"	2"	2.75"	2"	2"	1"	1"	1.5"
With docking	-	-	-	-	-	-	-	-	-
USB powered	-	-	-	-	Yes	Yes	Yes	Yes	Yes
Aux-in	Yes	Yes	-	Yes	-	-	-	-	-
Headphone out	Yes	Yes	Yes	Yes	-	-	-	-	-
Others	-	-	-	-	-	-	Wood finishing	Clip on top	Clip on top

2.1 PC speakers



	SPA7380	SPA7355	SPA5300	SPA4355	SPA4350	SPA2335	SPA1330
Output power RMS	60W	50W	50W	30W	30W	28W	10W
Satellite driver size	3"	2.75"	3"	2.5"	2.5"	2.5"	2"
Tweeter	-	Yes, mylar	-	-	-	-	-
Subwoofer driver size	5.25"	5.25"	5.25"	5"	5"	5"	4"
Vol. control	On wired control	On satellite	On wired control	On wired control	On subwoofer	On wired control	On subwoofer
Aux-in	Yes	Yes	-	Yes	-	-	-
Headphone out	Yes	Yes	-	Yes	-	-	-



SPA7220



SPA1260



Look and sound powerful

2.0 PC speakers SPA8210

Packing a powerful wOOx bass and a high-definition silk dome tweeter in a stylish aluminum-fronted cabinet, Philips SPA8210 speakers look and sound just wonderful!



wOOx™ loudspeaker technology for deep and powerful bass



Silk dome tweeter for crystal clear sound



Aluminum metal front - curved to create an ideal acoustic chamber, optimizes audio delivery for sound



SPA7355




SPA4355

Takes gaming to a new level

2.1 PC speakers SPA7380

Four sophisticated integrated circuits drive the subwoofer and two satellite speakers for powerful sound while Philips SPD bass port technology delivers pure deep bass, and all with 60W output for the explosive bass that gamers want.



60W output power for powerful sound and explosive bass



SPD™ innovative bass port technology for deep, rounded tones



Advanced integrated circuits provide quality sound and all the power needed to drive the subwoofer and satellites



www.philips.com

© 2012 Koninklijke Philips Electronics N.V.  
 All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent or other industrial or intellectual property rights.