

DVD Video Player
DVD 711

Philips DVD-Video Player DVD 711

- DVD / Video CD / Audio CD / CD-R / CD-RW playback
- Dual Laser optical pickup unit
- Perfect Still picture with multiple Zoom
- Enhanced Parental Control with Disc Lock
- 5 Disc resume
- Advanced DVD-Video technology, including 10-bit video DAC and 24-bit audio DAC
- TruSurround 3D Sound for analog out
- Audio and video bit rate indicator
- Digital Audio / Optical output (PCM / MPEG/ AC-3/ DTS)

TruSurround
with SRS (●)

DOLBY
DIGITAL

Rewritable
CD
COMPATIBLE

COMPACT
disc
DIGITAL AUDIO

DVD
VIDEO

dts
DIGITAL OUT

ZOOM
+ perfect still



Let's make things better.



PHILIPS

DVD Video Player

DVD 711

Technical Specifications DVD 711

Playback System

- DVD Video
- Video CD
- CD (CD-R and CD-RW)

Optical Read-out System

- Laser type Semiconductor AlGaAs
- Numerical Aperture 0.6 (DVD)
0.45 (VCD/CD)
- Wavelength 650 nm (DVD)
780 nm (VCD/CD)

DVD Disc Format

- Medium Optical disc
- Diameter 12 cm (8 cm)
- Playing time (12 cm)
 - one layer 2.15h¹
 - dual layer 4h¹
 - two side, single layer 4.30h¹
 - two side, dual layer 8h¹

TV Standard

- | | | |
|-------------------|--------------------------|-------|
| | PAL | NTSC |
| | 50 Hz | 60 Hz |
| • Number of lines | 625 | 525 |
| • Playback | Multistandard (PAL/NTSC) | |

Video Format

- DA Converter 10 bits
- Signal handling Components
- Digital Compression MPEG2 for DVD
MPEG1 for VCD

- | | | |
|--------------------|-------------------------|-------------------------|
| <i>DVD</i> | 50 Hz | 60 Hz |
| • Hor. Resolution | 720 pixels ² | 720 pixels ² |
| • Vert. Resolution | 576 lines | 480 lines |
| <i>VCD</i> | | |
| • Hor. Resolution | 352 pixels | 352 pixels |
| • Vert. Resolution | 288 lines | 240 lines |

Video Performance

- Video output 1 V_{pp} into 75 Ohm
- S-Video output Y: 1 V_{pp} into 75 Ohm
C: 0.3 V_{pp} into 75 Ohm
- RGB output 0.7 V_{pp} into 75 Ohm
- Black Level Shift On/Off
- Video Shift Left/Right

Audio Format

- Digital MPEG/ DTS/AC-3 Compressed Digital
PCM 16, 20, 24 bits
fs, 48, 96 kHz
- Analog Sound Stereo
Dolby Pro Logic downmix from AC-3 multichannel sound
3D Sound for virtual 5.1 channel sound on 2 speakers

Audio Performance

- DA Converter 24 bits
- DVD
 - f_s 96 kHz 4 Hz-44 kHz
 - f_s 48 kHz 4 Hz-22 kHz
- Video CD
 - f_s 48 kHz 4 Hz-22 kHz
 - f_s 44.1 kHz 4 Hz-20 kHz
- Signal-Noise (1 kHz) 103 dB
- Dynamic Range (1 kHz) 98 dB
- Crosstalk (1 kHz) 115 dB
- Distortion / Noise (1 kHz) 95 dB

Connections

- SCART 2 Euroconnector
- S-Video Output Mini DIN, 4-pins
- Video Output Cinch (yellow)
- Audio L+R Output Cinch (white/red)
- Digital Output 1 coaxial, 1 optical
IEC958 for CDDA / LPCM
IEC1937 for MPEG1/2, AC-3, DTS

Power Supply

- Power Inlet 230 V, 50 Hz
- Power usage 20 Watt
- Power usage standby less than 5 Watt

Cabinet

- Dimensions 435 x 92 x 320 mm
(W x H x D)
- Weight Approx. 4 Kg

Package Contents

- DVD-Video Player
- Remote Control with batteries
- AC Power Cord
- User Manual
- Audio cable
- Video cable
- SCART cable (Euroconnector)

Carton

- Colors Four color printing on white box
- Languages English (front, top)
French (rear)
Spanish (right)
German (left)

General Functionality

- Stop / Play / Pause
- Fast Forward/Backward
- Time Search
- Step Forward/Backward
- Slow
- Title / Chapter / Track Select
- Skip Next / Skip Previous
- Repeat (Chapter / Title / All) or (Track / All)
- A-B Repeat
- Shuffle
- Enhanced ease of use graphical interface
- Perfect Still with digital multi-tap filter
- Zoom (x1.33, x2, x4) with picture enhancement
- 3D sound
- Virtual Jog Shuttle
- Audio and video bit rate indicator (only available in certain countries)

DVD Functionality

- Multi-angle Selection
- Audio Selection (1 out of max. 8 languages)
- Subtitles Selection (1 out of max. 32 languages)
- Aspect Ratio conversion (16:9, 4:3 Letterbox, 4:3 Pan Scan)
- Parental Control and Disc lock
- Disc Menu support (Title Menu and Root Menu)
- Resume (5 discs) after stop / standby
- Screen Saver (*Dim 75% after 15 min.*)
- Programming Titles/chapters with Favourite Selection

Video CD Functionality

- Playback Control for VCD 2.0 discs
- Parental Control and Disc lock
- Resume (5 discs) after stop / standby
- Screen Saver (*Dim 75% after 15 min.*)
- Programming Tracks with Favourite Selection

Audio CD Functionality

- Time Display (Total / Track / Remaining Track Time)
- Full audio functionality with remote control
- Programming with Favourite Track Selection
- 1 Typical playing time for movie with 2 spoken languages and 3 subtitle languages.
- 2 Equivalent to 500 lines on your TV

Philips Disc Systems
P.O. Box 80002
5600 JB Eindhoven
The Netherlands

<http://www.sv.philips.com>