

DVD Video Player  
**DVD 761**

## Philips DVD-Video Player DVD 761

- DVD / Video CD / Audio CD / CD-R / CD-RW playback
- 6-channel analog output for Dolby Digital™, Dolby Pro Logic™ and stereo
- Dual Laser optical pickup unit
- Smart Picture for personal video preferences
- 5 Disc Resume
- Advanced DVD-Video technology, including 10-bit video DAC and 24-bit audio DAC
- TruSurround 3D Sound for analog out
- Cinemalink for one touch Home Cinema control
- Enhanced Parental Control with Disc Lock
- Perfect Still picture with multiple Zoom
- Audio and video bit rate indicator
- Digital Audio / Optical output (PCM / MPEG / AC-3 / DTS)
- Headphone connector with volume control



Let's make things better.



**PHILIPS**

# DVD Video Player

## DVD 761

### Technical Specifications DVD 761

#### Playback System

- DVD Video
- Video CD
- CD (CD-R and CD-RW)

#### Optical Read-out System

- Laser type Semiconductor AlGaAs
- Numerical Aperture 0.6 (DVD)  
0.45 (VCD/CD)
- Wavelength 650 nm (DVD)  
780 nm (VCD/CD)

#### DVD Disc Format

- Medium Optical disc
- Diameter 12 cm (8 cm)
- Playing time (12 cm)
  - one layer 2.15h<sup>1</sup>
  - dual layer 4h<sup>1</sup>
  - two side, single layer 4.30h<sup>1</sup>
  - two side, dual layer 8h<sup>1</sup>

#### TV Standard

- |                   |                          |       |
|-------------------|--------------------------|-------|
|                   | PAL                      | NTSC  |
|                   | 50 Hz                    | 60 Hz |
| • Number of lines | 625                      | 525   |
| • Playback        | Multistandard (PAL/NTSC) |       |

#### Video Format

- DA Converter 10 bits
- Signal handling Components
- Digital Compression MPEG2 for DVD  
MPEG1 for VCD

- |                    |            |            |
|--------------------|------------|------------|
| <i>DVD</i>         | 50 Hz      | 60 Hz      |
| • Hor. Resolution  | 720 pixels | 720 pixels |
| • Vert. Resolution | 576 lines  | 480 lines  |
| <i>VCD</i>         |            |            |
| • Hor. Resolution  | 352 pixels | 352 pixels |
| • Vert. Resolution | 288 lines  | 240 lines  |

#### Video Performance

- Video output 1 V<sub>pp</sub> into 75 Ohm
- S-Video output Y: 1 V<sub>pp</sub> into 75 Ohm  
C: 0.3 V<sub>pp</sub> into 75 Ohm  
0.7 V<sub>pp</sub> into 75 Ohm
- RGB
- Black Level Shift On/Off
- Video Shift Left/Right

#### Audio Format

- Digital MPEG/ DTS/AC-3 Compressed Digital  
PCM 16, 20, 24 bits  
fs, 48, 96 kHz
- Analog Sound Stereo  
Dolby Pro Logic downmix from AC-3 multichannel sound  
Full decoding of Dolby Digital multi-channel surround sound  
3D Sound for virtual 5.1 channel sound on 2 speakers

#### Audio Performance

- DA Converter 24 bits
- DVD
  - f<sub>s</sub> 96 kHz 4 Hz-44 kHz
  - f<sub>s</sub> 48 kHz 4 Hz-22 kHz
- Video CD
  - f<sub>s</sub> 48 kHz 4 Hz-22 kHz
- CD
  - f<sub>s</sub> 44.1 kHz 4 Hz-20 kHz
- Signal-Noise (1 kHz) 103 dB
- Dynamic Range (1 kHz) 98 dB
- Crosstalk (1 kHz) 113 dB
- Distortion / Noise (1 kHz) 92 dB
- Headphone 30 mW at 32 Ohm load
- Headphone impedance 8-2k Ohm

#### Connections

- Scart 2 Euroconnector
- S-Video Output Mini DIN, 4-pins
- Video Output Cinch (yellow)
- Audio L+R Output Cinch (white/red)
- Audio Front Left/Right Cinch (white/red)
- Audio Surr. Left/Right Cinch (white/red)
- Audio Centre Cinch (blue)
- Audio Subwoofer Cinch (black)
- Digital Output 1 coaxial, 1 optical  
IEC958 for CDDA / LPCM  
IEC1937 for MPEG1/2, AC-3, DTS  
on SCART
- Cinematic Headphone 6.3 mm Jack

#### Power Supply

- Power Inlet 230 V, 50 Hz
- Power usage Approx. 20 Watt
- Power usage standby Approx. 5 Watt

#### Cabinet

- Dimensions 435 x 92 x 320 mm  
(W x H x D)
- Weight Approx. 4 Kg

#### Package Contents

- DVD-Video Player
- Remote Control with batteries
- AC Power cord
- User Manual
- Audio cable
- Video cable
- Scart cable (Euroconnector)

#### Carton

- Colors Four color printing on white box
- Languages English (front, top)  
French (rear)  
Spanish (right)  
German (left)

#### General Functionality

- Stop / Play / Pause
- Fast Forward/Backward
- Time Search
- Step Forward/Backward
- Slow
- Title / Chapter / Track Select
- Skip Next / Skip Previous
- Repeat (Chapter / Title / All) or (Track / All)
- A-B Repeat
- Shuffle
- Scan
- Enhanced ease of use graphical interface
- Perfect Still with digital multi-tap filter
- Zoom (x1.33, x2, x4) with picture enhancement
- Smart Picture
- Cinematic interconnection for plug&play
- 3D sound
- Per speaker setting of Volume, Delay, Range
- Virtual Jog Shuttle
- Audio and video bit rate indicator (only available in certain countries)
- Beeper (only available in certain countries)

#### DVD Functionality

- Multi-angle Selection
- Audio Selection (1 out of max. 8 languages)
- Subtitles Selection (1 out of max. 32 languages)
- Aspect Ratio conversion (16:9, 4:3 Letterbox, 4:3 Pan Scan)
- Parental Control and Disc lock
- Disc Menu support (Title Menu and Root Menu)
- Resume (5 discs) after stop / standby
- Screen Saver (*Dim 75% after 15 min.*)
- Programming Titles/chapters with Favourite Selection

#### Video CD Functionality

- Playback Control for VCD 2.0 discs
- Disc lock
- Resume (5 discs) after stop / standby
- Screen Saver (*Dim 75% after 15 min.*)
- Programming Tracks with Favourite Selection

#### Audio CD Functionality

- Time Display (Total / Track / Remaining Track Time)
- Full audio functionality with remote control
- Programming with Favourite Track Selection

- 1 Typical playing time for movie with 2 spoken languages and 3 subtitle languages.

Philips Disc Systems  
P.O. Box 80002  
5600 JB Eindhoven  
The Netherlands

<http://www.philips.com>