

Philips
DVD recorder/VCR with
i.LINK digital input



DVDR3435V

Preserve your VHS tapes on DVD

Introducing the all-in-one player that plays and records on both DVD discs and VHS tapes! With i.LINK you can now copy your favourite camcorder tapes in perfect digital picture and sound quality to DVD.

Record, transfer or archive conveniently

- i.LINK digital input for perfect digital camcorder copies
- Direct Dubbing - simply record your videos from VHS to DVD

Plays and records what you want

- Dual Media conveniently records on both DVD+R/RW & DVD-R/RW
- Plays DVD, CD, DVD+R/RW, DVD-R/RW, (S)VCD, VHS tapes
- Plays MP3, WMA, JPEG, DivX 3.11/4.x/5.x/6

Simplicity in recording and playback

- VCR Plus+ for quick and easy programming


Superior audio and video quality

- Progressive Scan component video for optimized image quality

PHILIPS
sense and simplicity

Highlights

i.LINK digital input



Also known as IEEE 1394 and FireWire, i.Link carries all audio and video signals via a single cable digitally, with no loss in picture and sound quality. With i.Link digital video input, you can copy your home videos in their original digital picture quality.

Direct Dubbing (VHS to DVD)

Having a Direct Dubbing button allows for the user to start recording from the video tape without complicated menu system selection or input/output selection for separates.

Dual Media

Philips DVD Recorders support 'dual media' recording – the ability to create recordings on DVD+R/RW and DVD-R/RW discs. Now you can buy any disc and your Philips recorder will always create fully compatible recordings, which can be played on any DVD player.

Multi-format playability(DivX)


Multi-format playability allows you to play most file formats for maximum listening and viewing pleasure, including MP3, WMA, JPEG and the popular DivX digital media format. DivX playback enables you to play and share compressed high quality DivX video content beyond your computer.

VCR Plus+

With the VCR Plus+ system, all you need to do to program your video recorder is to enter the 'Pluscode' – a single code of up to nine digits

(but usually less) that is printed next to each TV program in most TV guides.

Progressive Scan



Progressive Scan doubles the vertical resolution of the image resulting in a noticeably sharper picture. Instead of sending a field comprising the odd lines to the screen first, followed by the field with the even lines, both fields are written at one time. A full image is created instantaneously, using the maximum resolution. At such a speed, your eye perceives a sharper picture with no line structure.



Specifications

Picture/Display

- A/D converter: 10 bit, 54 MHz
- D/A converter: 10 bit, 54 MHz
- Picture enhancement: Progressive Scan

Sound

- A/D converter: 24 bit, 192 kHz
- D/A converter: 24 bit, 192 kHz

Video Recording

- Recording system: NTSC
- Compression formats: MPEG2
- Recording Modes: High Quality (HQ), Standard Play (SP), Standard Play Plus (SPP), Long Play (LP), Extended Play (EP), Super Long Play (SLP)
- Recording enhancements: Append, Chapter Marker Insertion, Divide, Erase, Manual Chapter Marking, One Touch Record (OTR), Safe Record, Selectable Index Pictures
- Audio compression: Dolby Digital
- Recording Media: DVD+R/+RW, DVD-R/-RW, VHS Tapes

Video Playback

- Playback Media: DVD-Video, CD-R/CD-RW, DVD+R/+RW, DVD-R/-RW, Video CD/SVCD, VHS Tapes
- Compression formats: MPEG2, MPEG1, DivX 3.11, DivX 4.x, DivX 5.x, DivX 6.0
- Video tape playback system: NTSC, PAL

Audio Playback

- Playback Media: Audio CD, CD-R/RW
- Compression format: Dolby Digital, MP3, WMA
- Number of Audio Heads: 2 Hi-Fi

Still Picture Playback

- Playback Media: DVD+R/+RW, DVD-R/-RW, CD-R/RW
- Picture compression format: JPEG
- Picture enhancement: Rotate, Zoom, Flip photos

Tuner/Reception/Transmission

- TV system: NTSC
- No. of preset TV Channels: 180

Connectivity

- Front / Side connections: i.LINK DV in (IEEE1394, 4-pin), S-video in, CVBS in, Audio L/R in
- Rear Connections: Digital coaxial out, Composite video (CVBS) output, S-Video in, S-Video out, RF antenna in / TV out, Analog audio Left/Right in, Composite video (CVBS) input, Analog audio Left/Right out 2x

Convenience

- Programmable Events: 8
- Programming/Timer Enhancements: VCR Plus+, One Touch Recording, Daily/Weekly Repeat Program, Manual Timer
- Programming Period: 1 month

Power

- Power supply: 120V, 60Hz
- Power consumption: 30 W
- Standby power consumption: < 3 W

Accessories

- Included Accessories: Quick start guide, Remote Control, User Manual, RF antenna cable, 2 x AAA Batteries, Product Registration Card, Audio/Video cable

Dimensions

- Set dimensions (W x H x D): 435 x 99.5 x 262 mm
- Set weight: 4.3 kg
- Packaging dimensions (W x H x D): 542 x 180 x 375 mm
- Weight incl. Packaging: 5.6 kg



Issue date 2009-04-21

Version: 6.0.12

12 NC: 8622 810 13241
UPC: 6 09585 11203 2

© 2009 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com