

Philips
Hard disk/DVD recorder

160 GB

DVDR3450H



VIDEO Plus+

Watch what you want when you want

Record on Hard Disk without having to worry where to store it. Keep what you like on DVD in lasting quality.

Record, transfer or archive conveniently

- Record more than 250 hrs of TV on a 160 GB Hard Disk
- High-speed archiving from Hard Disk to DVD
- i.LINK digital input for perfect digital camcorder copies

Plays and records what you want

- Plays MP3, WMA, JPEG, DivX 3.1 | 4.x/5.x/6
- Dual Media conveniently records on both DVD+R/RW & DVD-R/RW
- Plays CD, (S) VCD, DVD, DVD+R/RW, DVD-R/RW

Simplicity in recording and playback

- One Touch Pause Live TV freezes the action instantly
- Instant Replay for reliving a live TV moment with one touch
- VIDEO Plus+ for quick and easy programming



PHILIPS
sense and simplicity

Hard disk/DVD recorder
160 GB

Specifications

Picture/Display

- **D/A converter:** 10-bit, 54 MHz
- **A/D converter:** 10-bit, 54 MHz

Sound

- **D/A converter:** 24-bit, 96 kHz
- **A/D converter:** 24-bit, 96 kHz

Video Recording

- **Recording system:** PAL
- **Compression formats:** MPEG2
- **Recording Modes:** High Quality (HQ), Standard Play (SP), Standard Play Plus (SPP), Long Play (LP), Extended Play (EP), Super Long Play (SLP), Super Extended Play (SEP)
- **Audio compression:** Dolby Digital
- **Recording Media:** DVD+R/+RW, DVD-R/-RW

Video Playback

- **Playback Media:** CD-R/CD-RW, DVD+R/+RW, DVD-R/-RW, DVD-Video, Video CD/SVCD, DVD+R DL, DVD-R DL
- **Compression formats:** MPEG2, MPEG1, DivX 3.11, DivX 4.x, DivX 5.x, DivX 6.0, MPEG4

Audio Playback

- **Playback Media:** Audio CD, CD-R/RW
- **Compression format:** Dolby Digital, MP3, MPEG2 Multi-channel, PCM, WMA

Still Picture Playback

- **Playback Media:** CD-R/RW
- **Picture compression format:** JPEG
- **Picture enhancement:** Slideshow with MP3 playback

Storage Media

- **Hard Disk Capacity:** 160 GB
- **HDD recording enhancements:** Instant Replay,

Pause Live TV

Tuner/Reception/Transmission

- **TV system:** PAL I, PAL B/G, PAL D/K, SECAM B/G, SECAM D/K, SECAM L/L'

Connectivity

- **Front/Side connections:** Audio L/R in, CVBS in, i.LINK DV in (IEEE1394, 4-pin), S-video in
- **Rear Connections:** Analogue audio Left/Right out, Composite video (CVBS) output, Digital coaxial out, RF antenna in/TV out, S-Video out, SCART I (CVBS, RGB out), SCART2 (CVBS, RGB in)

Convenience

- **Programming/Timer Enhancements:** Daily/Weekly Repeat Programme, Manual Timer, One Touch Recording, VIDEO Plus+, VPS/PDC recording control
- **Programmable Events:** 8

Electricity

- **Power supply:** 220-240 V
- **Power consumption:** 50 W
- **Standby power consumption:** 3.0 W

Accessories

- **Included Accessories:** Quick start guide, User Manual, Antenna cable, Full SCART cable, Power cord, Remote Control, 2 x AAA Batteries
- **Remote Control I2NC:** 242254901243

Dimensions

- **Set dimensions (W x H x D):** 435 x 43 x 340 mm
- **Packaging dimensions (W x H x D):** 571 x 123 x 412 mm
- **Set weight:** 3.6 kg
- **Weight incl. Packaging:** 6 kg

DVDR3450H/05

Product highlights

i.LINK digital input

Also known as IEEE 1394 and FireWire, i.Link carries all audio and video signals via a single cable digitally, with no loss in picture and sound quality. With i.Link digital video input, you can copy your home videos in their original digital picture quality.

Multi-format playability (DivX)

Multi-format playability allows you to play most file formats, including MP3, WMA, JPEG and the popular DivX digital media format, for maximum listening and viewing pleasure. DivX playback enables you to play and share compressed high-quality DivX video content beyond your computer.

Dual Media

Philips DVD Recorders support 'dual media' recording — the ability to create recordings on DVD+R/RW and DVD-R/RW discs. Now you can buy any disc and the Philips recorder will always create fully compatible recordings that can be played by any DVD player.

One Touch Pause Live TV

Pause Live TV puts you in absolute control. Once the recorder is turned on, a large built-in memory automatically starts recording the programme you are watching — allowing you to pause, replay or save the programme, any time. If you need to take a break, you can pause your 'live' TV programme with just one touch of a button, and resume watching when it suits you.

Instant Replay

With Instant Replay, you can relive magic movie moments and super sports scenes - any time you want. At the touch of a button, the hard disk will replay the last 30 seconds. Skipping further backwards requires nothing more than pressing the button again.

VIDEO Plus+

With the VIDEO Plus+ system, all you need to do to programme your video recorder is to enter the "Pluscode" — a single code of up to nine digits (but usually fewer) that is printed next to each TV programme in most TV guides.



Issue date 2009-02-12

Version: 5.1.9

12 NC: 8622 810 12952
EAN: 87 10895 93871 6

© 2009 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com