

Philips
Hard disk/DVD recorder

160 GB

DVDR3455H



Watch what you want when you want

Record on Hard Disk without having to worry where to store it. Keep what you like on DVD in lasting quality.

Record, transfer or archive conveniently

- Record more than 250 hrs of TV on a 160 GB Hard Disk
- USB Direct plays photos and music from USB flash drives
- High-speed archiving from Hard Disk to DVD
- i.LINK digital input for perfect digital camcorder copies

Simplicity in recording and playback

- One Touch Pause Live TV freezes the action instantly
- Instant Replay for reliving a live TV moment with one touch
- G-CODE for quick and easy programming

Plays and records what you want

- Plays MP3, WMA, JPEG, DivX 3.11/4.x/5.x/6
- Dual Media conveniently records on both DVD+R/RW & DVD-R/RW
- Plays CD, (S)VCD, DVD, DVD+R/RW, DVD-R/RW

PHILIPS

Hard disk/DVD recorder
160 GB

DVDR3455H/96

Highlights

160 GB hard disk (250 hrs)

Record more than 250 hrs of TV on a 160 GB Hard Disk

USB Direct

Simply plug your device into the USB port on your Philips DVD system. Your digital music and photos will be played directly from the device. Now you can share your favorite moments with family and friends.

Multi-format playability(DivX)

Multi-format playability allows you to play most file formats for maximum listening and viewing pleasure, including MP3, WMA, JPEG and the popular DivX digital media format. DivX playback enables you to play and share

compressed high quality DivX video content beyond your computer.

Dual Media

Philips DVD Recorders support 'dual media' recording – the ability to create recordings on DVD+R/RW and DVD-R/RW discs. Now you can buy any disc and your Philips recorder will always create fully compatible recordings, which can be played on any DVD player.

One Touch Pause Live TV

Pause Live TV puts you in absolute control. Once the recorder is turned on, a large built-in memory automatically starts recording the program you are watching -- allowing you to pause, replay or save the program, anytime. If you need to take a break, you can pause your

'live' TV program with just one touch of a button, and resume watching when it suits you.

Instant Replay

With Instant Replay, you can relive magic movie moments and super sports scenes - anytime you want. At the touch of a button, the hard disk will replay the last 30 seconds. Skipping backwards further requires nothing more than pressing the button again.

G-CODE

With the G-CODE system, all you need to do to program your video recorder is entering the G-CODE number – a single code of up to nine digits (but usually less) that is printed next to each TV program in most TV guides.



DIVX



G-CODE

Specifications

Picture/Display

- D/A converter: 10 bit, 54 MHz
- A/D converter: 10 bit, 54 MHz
- Picture enhancement: Progressive scan

Sound

- D/A converter: 24 bit, 96 kHz
- A/D converter: 24 bit, 96 kHz

Video Recording

- Recording system: NTSC, PAL
- Compression formats: MPEG2
- Recording Modes: High Quality (HQ), Standard Play (SP), Standard Play Plus (SPP), Long Play (LP), Extended Play (EP), Super Long Play (SLP), Super Extended Play (SEP)
- Audio compression: Dolby Digital
- Recording Media: DVD+R/+RW, DVD-R/-RW

Video Playback

- Playback Media: CD-R/CD-RW, DVD+R/+RW, DVD-R/-RW, DVD-Video, Video CD/SVCD, DVD+R DL, DVD-R DL
- Compression formats: MPEG2, MPEG1, DivX 3.11, DivX 4.x, DivX 5.x, MPEG4, DivX 6.0

Audio Playback

- Playback Media: Audio CD, CD-R/RW
- Compression format: Dolby Digital, MP3, MPEG2 Multichannel, PCM

Still Picture Playback

- Playback Media: CD-R/RW
- Picture Compression Format: JPEG
- Picture Enhancement: Slideshow with MP3 playback

Storage Media

- Hard Disk Capacity: 160 GB
- HDD recording enhancements: Instant Replay,

Pause Live TV

Tuner/Reception/Transmission

- TV system: PAL B/G, PAL D/K, PAL I, SECAM D/K, SECAM L/L'

Connectivity

- Front / Side connections: Audio L/R in, CVBS in, i.LINK DV in (IEEE1394, 4-pin), S-video in, USB
- Rear Connections: Analog audio Left/Right in, Analog audio Left/Right out 2x, Component Video output, Composite video (CVBS) input, Composite video (CVBS) output, Digital coaxial out, RF antenna in / TV out, S-Video out

Convenience

- Programming/Timer Enhancements: Daily/Weekly Repeat Program, Manual Timer, One Touch Recording, VCR Plus+
- Programmable Events: 20

Power

- Power supply: 110-240V
- Power consumption: 50 W
- Standby power consumption: 3.0W

Accessories

- Included accessories: 2 x AAA Batteries, Antenna cable, Audio/Video cable, Power cord, Quick start guide, Remote Control, User Manual
- Remote Control 12NC: 242254900971

Dimensions

- Set dimensions (W x H x D): 435 x 48 x 325 mm
- Packaging dimensions (W x H x D): 570 x 125 x 425 mm
- Set weight: 3.6 kg
- Weight incl. Packaging: 5.5 kg



Issue date 2014-02-10

Version: 1.0.5

12 NC: 8670 000 26317
EAN: 87 12581 30812 4

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com