

Philips
Hard Disk/DVD Recorder

250 GB

DVDR3460H



Watch what you want when you want

Record on Hard Disk without having to worry where to store it. Keep what you like on DVD in lasting quality.

Record, transfer or archive conveniently

- Record more than 400 hrs of TV on a 250 GB hard disk
- USB Direct plays photos and music from USB flash drives
- High-speed archiving from Hard Disk to DVD
- i.LINK digital input for perfect digital camcorder copies

Plays and records what you want

- Plays MP3, WMA, JPEG, DivX 3.11/4.x/5.x/6
- Dual Media records on both DVD+R/RW and DVD-R/RW
- Plays CD, (S)VCD, DVD, DVD+R/RW, DVD-R/RW

Simplicity in recording and playback

- One Touch Pause Live TV freezes the action instantly
- Instant Replay for reliving a live TV moment with one touch
- VIDEO Plus+ for quick and easy programming



PHILIPS

sense and simplicity

Specifications

Picture/Display

- **D/A converter:** 10 bit, 54 MHz
- **A/D converter:** 10 bit, 54 MHz

Sound

- **D/A converter:** 24 bit, 96 kHz
- **A/D converter:** 24 bit, 96 kHz

Video Recording

- **Recording system:** PAL
- **Compression formats:** MPEG2
- **Recording Modes:** High Quality (HQ), Standard Play (SP), Standard Play Plus (SPP), Long Play (LP), Extended Play (EP), Super Long Play (SLP), Super Extended Play (SEP)
- **Audio compression:** Dolby Digital
- **Recording Media:** DVD+R/+RW, DVD-R/-RW

Video Playback

- **Playback Media:** CD-R/CD-RW, DVD+R/+RW, DVD-R/-RW, DVD-Video, Video CD/SVCD, DVD+R DL, DVD-R DL
- **Compression formats:** MPEG2, MPEG1, DivX 3.11, DivX 4.x, DivX 5.x, DivX 6.0, MPEG4

Audio Playback

- **Playback Media:** Audio CD, CD-R/RW
- **Compression format:** Dolby Digital, MP3, MPEG2 Multichannel, PCM, WMA

Still Picture Playback

- **Playback Media:** CD-R/RW
- **Picture compression format:** JPEG
- **Picture enhancement:** Slideshow with MP3 playback

Storage Media

- **Hard Disk Capacity:** 250 GB
- **HDD recording enhancements:** Instant Replay,

Pause Live TV

Tuner/Reception/Transmission

- **TV system:** PAL I, PAL B/G, PAL D/K, SECAM B/G, SECAM D/K, SECAM L/L'

Connectivity

- **Front / Side connections:** Audio L/R in, CVBS in, i.LINK DV in (IEEE1394, 4-pin), S-video in, USB
- **Rear Connections:** Analogy audio Left/Right out, Composite video (CVBS) output, Digital coaxial out, RF antenna in / TV out, S-Video out, SCART I (CVBS, RGB out), SCART2 (CVBS, RGB in)

Convenience

- **Programming/Timer Enhancements:** Daily/Weekly Repeat Program, Manual Timer, One Touch Recording, VIDEO Plus+, VPS/PDC recording control
- **Programmable Events:** 8

Power

- **Power supply:** 220-240V
- **Power consumption:** 50 W
- **Standby power consumption:** 3.0W

Accessories

- **Included Accessories:** Antenna cable, Power cord, Quick start guide, Remote Control, User Manual, 2 x AAA Batteries, Full SCART cable
- **Remote Control I2NC:** 242254901243

Dimensions

- **Set dimensions (W x H x D):** 435 x 43 x 340 mm
- **Packaging dimensions (W x H x D):** 571 x 123 x 412 mm
- **Set weight:** 3.6 kg
- **Weight incl. Packaging:** 6 kg

Product highlights

USB Direct

Simply plug your device into the USB port on your Philips DVD system. Your digital music and photos will be played directly from the device. Now you can share your favourite moments with family and friends.

i.LINK digital input

Also known as IEEE 1394 and FireWire, i.Link carries all audio and video signals via a single cable digitally, with no loss in picture and sound quality. With i.Link digital video input, you can copy your home videos in their original digital picture quality.

Multi-format playability(DivX)

Multi-format playability allows you to play most file formats for maximum listening and viewing pleasure, including MP3, WMA, JPEG and the popular DivX digital media format. DivX playback enables you to play and share compressed high quality DivX video content beyond your computer.

Dual Media

Philips DVD Recorders support 'dual media' recording - the ability to create recordings on DVD+R/RW and DVD-R/RW discs. Now you can buy any disc and the Philips recorder will always create fully compatible recordings, which can be played by any DVD player.

One Touch Pause Live TV

Pause Live TV puts you in absolute control. Once the recorder is turned on, a large built-in memory automatically starts recording the program you are watching, allowing you to pause, replay or save the program, anytime. If you need to take a break, you can pause your 'live' TV program with just one touch of a button and resume watching when it suits you.

Instant Replay

With Instant Replay you are in control of exciting TV moments so you can enjoy a precious TV moment like a scene in a movie or football match again, at the press of a button. The Hard Disk can play back any scene while continuing to record TV program.

VIDEO Plus+

With the VIDEO Plus+ system, all you need to do to program your video recorder is to enter the 'Pluscode' - a single code of up to nine digits (but usually less) that is printed next to each TV program in most TV guides.



Issue date 2007-11-13

Version: 5.0

12 NC: 8622 810 12943
EAN: 87 10895 93864 8

© 2007 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com