

Philips
DVD Recorder/Hard Disk
with FlexTime and i.LINK
digital input



DVDR725H

DVD Recorder/Hard Disk

Record today on Hard Disk and preserve for life

Record anything without having to worry ever again where to store it. Keep what you like in lasting digital quality on DVD

The perfect recording solution

- Record more than 250 hrs of TV on a 160 GB Hard Disk
- High-speed archiving from HDD to DVD at up to 20x speed
- One Touch Pause Live TV freezes the action instantly
- Instant Replay for reliving a live TV moment with one touch
- FlexTime to watch the beginning while you record the end

TV Recording made simple!

- Guide Plus+ electronic on-screen TV guide
- Favorite Show Selection automatically record every episode
- Infrared control for recording from set-top box

Preserve your favorite memories on DVD

- Smart chaptering adds scene-based chapter markers via i.LINK
- i.LINK digital input for perfect digital camcorder copies

Share your favorite recordings

- Your DVDs will play on existing DVD players and drives

PHILIPS

Highlights

160 GB hard disk (250 hrs)

Record more than 250 hrs of TV on a 160 GB Hard Disk

High-Speed archiving:20x speed

High speed archiving lets you make a copy of a recording from Hard Disk to DVD in a fraction of the original recording time. Once the program is stored on HDD you can copy it to DVD+R/RW at maximum speed.

One Touch Pause Live TV

Pause Live TV puts you in absolute control. Once the recorder is turned on, a large built-in memory automatically starts recording the program you are watching -- allowing you to pause, replay or save the program, anytime. If you need to take a break, you can pause your 'live' TV program with just one touch of a button, and resume watching when it suits you.

Instant Replay

With Instant Replay, you can relive magic movie moments and super sports scenes - anytime you want. At the touch of a button, the hard disk will replay the last 30 seconds.

Skipping backwards further requires nothing more than pressing the button again.

FlexTime

With FlexTime you can watch a program while it's still being recorded, thanks to the extreme speed of a Hard Disk. You can also watch a different program from the Hard Disk while it's recording something else.

Guide Plus+ on-screen TV guide

GUIDE Plus+ is an Electronic Program Guide -- a free on-screen TV Guide that shows what's on TV for the next couple of days and lets you program the timer of the DVD Recorder with the push of a button.

Favorite Show Selection

Favorite Show Selection automatically record every episode

Set-top box infrared control

The Sat Mouse is a special accessory that lets a DVD Recorder control external satellite receivers. It sends infra-red remote control

commands in order to switch the satellite receiver on and select the correct channel.

Smart chaptering

Smart chaptering detects scene cuts (time/date changes) in the DV original to ensure the chapters in the DVD copy are lined up exactly.

i.LINK digital input

Also known as IEEE 1394 and FireWire, i.Link carries all audio and video signals via a single cable digitally, with no loss in picture and sound quality. With i.Link digital video input, you can copy your home videos in their original digital picture quality.

Two-Way Compatibility

DVD Recorders can play regular DVD-Video discs, but equally important is that DVD+R and DVD+RW discs recorded on them can be played on existing DVD-Video players.

Always compatible recordings

Always compatible recordings: with DVD+R/RW discs

FLEXTIME



Specifications

Connectivity

- Ext 2 Scart: S-video in, Decoder, CVBS in/out, RGB in, Audio in/out
- Ext 1 Scart: CVBS in/out, Audio in/out, RGB out, S-video out
- Front / Side connections: Audio L/R in, i.LINK DV in (IEEE1394, 4-pin), S-video in, Video in
- Other connections: Antenna IEC75, Digital coaxial out, Component Video out Interlaced, Analog audio Left/Right out, Digital optical out, Composite video (CVBS) out, IR mouse, S-Video out

Sound

- Crosstalk (1kHz): 105 dB
- D/A converter: 24 bit, 96 kHz
- A/D converter: 24 bit, 96 kHz
- Dynamic Range (1kHz): 90 dB
- Signal/noise ratio: 105

Picture/Display

- A/D converter: 9 bit, 27 MHz
- D/A converter: 10 bit, 54 MHz
- Color cabinet: precision silver

Video Playback

- Compression formats: MPEG1, MPEG2
- Playback Media: CD, CD-R, CD-RW, MP3-CD, DVD, DVD+RW, DVD-R, DVD-RW (Video mode), DVD-Video, SVCD, Video CD, DVD+R
- Disc Playback Modes: A-B Repeat, Chapter repeat, Disc Menu, Pause, Search forward/reverse, Shuffle Play, Fast Backward, Fast Forward, Framestep Forward, PBC, Resume Playback from Stop, Slow Motion, Zoom, Title Repeat
- DVD Region.: 2
- Video disc playback system: NTSC, PAL

Power

- Power supply: 200-240 V, 50Hz
- Standby power consumption: 3
- Power consumption: 38 W W

Accessories

- Included accessories: AC Power Cord, Coax RF antenna cable, Full SCART cable, Quick start guide, Remote Control, User Manual, Batteries for remote control, Safety & warranty booklet, IR extender cable
- Included batteries: 2x Longlife AA
- Printed User Guide
- Quick start guide
- Remote control: Zappa+
- Registration card: European version

Dimensions

- Carton dimensions (WxDxH) inch: 22.4 x 16.5 x 7.2
- Product dimension (WxDxH) inch: 17.1 x 13.2 x 3.0 inch
- Product weight (lb): 000 lb
- Product weight: 5.3 kg
- Weight incl. Packaging: 8 kg
- Temperature range (operation): 0°C to 40°C
- Carton dimensions (WxDxH): 570 x 420 x 182

mm

- Product dimensions (WxDxH): 435 x 335 x 76 mm

Green Specifications

- Packaging material: Carton
- User manual: Recycled paper

Convenience

- Child Protection: Child Lock
- User convenience: Electronic Programming Guide, Menu Languages
- Display Type: FTD
- Disc Library: Up to 9000 titles, Up to 999 discs
- Drop proof: 76 cm
- Ease of Installation: Autoinstall, Automatic Channel Install(ACI), Automatic Tuning System (ATS)
- Electronic Program Guide: GUIDE Plus+
- Front Controls: Cursor up/down/left/right, HDD, Record, play, stop, FF/NEXT, RWD/PREV, OK, Guide, Open/Close
- Language support: tbc
- On-Screen Display languages: Danish, Dutch, English, Finnish, French, German, Italian, Norwegian, Portuguese, Spanish, Swedish
- Pre-set Channels: 99
- Programming Period: 1 month
- Programmable Events: 12
- Programming/Timer Enhancements: Automatic Satellite Recording, Daily/Weekly Repeat Program, IR Set Top Box Control, Manual Timer, One Touch Recording, ShowView, VPS/PDC recording control
- Remote Control: Multi-brand
- Remote control: Zappa+
- Remote control type: RC19046006
- Compass GUI: HDD part Yes, DVD+RW no
- Ease To Experience: Demo Mode

Tuner/Reception/Transmission

- Aerial Input: 75 ohm coaxial (IEC75)
- TV system: PAL, SECAM
- Video Playback: NTSC, PAL, SECAM

Storage Media

- Extra Hard Disk Technology: Pause Live TV, Simultaneous Record & Playback
- Hard Disk Capacity: 160 GB
- HDD recording enhancements: Instant Jump, Instant Replay, Time Shift Buffer, Time Status Bar
- HDD to DVD copying: high-speed (direct copy)
- HDD video recording capacity: 250 hr
- Recording media: DVD+R, DVD+RW
- Recording speed: upto 20x on DVD+R in M8 mode

Audio Playback

- CD Playback Enhancements: Next/Previous Track, Repeat, Introscan, Shuffle
- Compression format: Dolby Digital, DTS, MP3, MPEG2 Multichannel, PCM
- Playback Media: CD, CD-R, CD-RW, MP3-CD
- Disc Playback Modes: Fast Forward/Backward, Next/Previous Album Search, Next/Previous Track Search
- File systems supported: ISO-9660

- ID3-tag support
- Loader Type: Motorised, Tray
- MP3 sample rates: 48, 44.1, 32 kHz

Video Recording

- Compression formats: MPEG2
- Max recording time on DVD: 8 hr
- Recording enhancements: Chapter Marker Insertion, Divide, Erase, Favorite Scene Selection, Manual Chapter Marking, One Touch Record (OTR), Program Name Recording, Safe Record, Selectable Index Pictures, Station ID Recording
- Recording Modes: M1: 60 minutes, M2: 120 minutes, M2x: 150 minutes, M3: 180 minutes, M4: 240 minutes, M6: 360 minutes, M8: 480 minutes
- Recording system: NTSC, PAL
- Audio compression: Dolby Digital



Issue date 2016-11-01

Version: 2.0.4

12 NC: 8622 810 12076
EAN: 87 10895 86469 5© 2016 Koninklijke Philips N.V.
All Rights reserved.Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com