

PHILIPS

Fully automatic
espresso machines

Series 3200

5 Beverages

LatteGo

Silver

Touch display

EP3246/70



5 delicious fresh bean coffees, easier than ever LatteGo, the fastest to clean milk system ever*

Easily make aromatic coffee varieties like Espresso, Coffee, Cappuccino and Latte Macchiato at the touch of a button. LatteGo tops milk varieties with silky smooth froth, is easy to set up and can be cleaned in as little as 15 seconds*

A variety of coffees customized to your taste

- Enjoy 5 coffees at your fingertips, including cappuccino
- Silky smooth milk froth thanks to high speed LatteGo system
- Easy selection of your coffee with intuitive touch display
- Adjust aroma strength and quantity via My Coffee Choice
- Easily adjust to your taste with 12-step grinder levels

High quality coffee from fresh beans

- The perfect temperature, aroma and crema cup after cup*
- 20,000 cups of finest coffee with durable ceramic grinders
- Keep your beans fresh for longer thanks to the aroma seal

Effortless use and cleaning for everyday enjoyment

- LatteGo is exceptionally easy to clean: 2 parts, no tubes
- Up to 5000 cups* without descaling thanks to AquaClean
- Easy cleaning thanks to fully removable brew group
- Dishwasher safe parts for your convenience

Highlights

5 aromatic coffees



Enjoy your favourite coffees for your special moments. Whether you crave for an espresso, a coffee or a milk based recipe, your fully-automatic espresso machine delivers a perfect in-cup result with no hassle and in no time!

LatteGo milk system



Top your coffee off with a silky-smooth layer of milk froth. The LatteGo mixes milk and air at high speed in the round frothing chamber, then adds a splash-free, creamy layer of milk froth to your cup at just the right temperature.

Intuitive touch display



The irresistible taste and aroma of coffee from fresh beans is just one touch away. Our intuitive touch display allows you to easily select your favorite coffee.

My Coffee Choice



Adjust the strength and quantity of your beverage with the My Coffee Choice menu. Easily choose from three different settings to suit your preferences.

12-step grinder adjustment



Our durable ceramic grinders can be adjusted in 12 steps, so you can turn your beans into anything from ultra-fine powder to coarse grindings.

Perfect temperature and aroma



The Aroma Extract system intelligently strikes the optimum balance between brewing temperature and aroma extraction by keeping the water temperature between 90 and 98°C, while regulating the water flow rate, so you can enjoy delicious coffees.

100% ceramic grinders



Our grinders are 100% pure ceramic: extremely hard and precise, so you can enjoy fresh aromatic coffee, for at least 20.000 cups.

2 parts, no tubes milk system



Our 2 parts milk system has no tubes or hidden parts and can be cleaned in as little as 15 seconds under tap* or in the dishwasher.

AquaClean filter



By changing the filter after being prompted by the machine, you will not need to descale your machine for up to 5000 cups*, while enjoying clear and purified water.

Specifications

Country of origin

Designed in: Italy
Made in: Romania

General specifications

Ease of cleaning & maintenance: AquaClean filter compatible
Milk Solution: LatteGo
User Interface: Touch screen display
Dishwasher safe parts: Drip tray, LatteGo
Adjustable spout height: 85-145 mm

Technical specifications

Capacity milk carafe: 0.26 L
Capacity waste container: 12 servings
Frequency: 50 Hz
Voltage: 230 V
Color & Finishing: Black, Silver Paint
Cord length: 100 cm
Filter compatibility: AquaClean
Waste container: Frontal access

Water tank: Frontal access
Weight of product: 8 kg
Product dimensions: 246x371x433 mm
Coffee bean capacity: 275 g
Capacity water tank: 1.8 L
Pump pressure: 15 bar

Customization

Aroma Strength Settings: 3
Grinder Settings: 12
Pre Brew Aroma control
Temperature settings: 3
Coffee and Milk Length: Adjustable

Variety

Beverages: Espresso, Hot water, Cappuccino, Coffee, Latte Macchiato, Americano
Coffee Powder Option
Double Cup
Milk Double Cup: No

Other features

Removable brew group
Aroma Seal
Guided descaling
AquaClean

Accessories

Included: AquaClean filter, Grease tube, Measuring scoop, Water hardness test strip, LatteGo storage lid

Service

2-year guarantee

Sustainability

ECO setting
Energy label: A-class
Power consumption brewing: 1500 W
Recyclable packaging material: >95 %

