

PHILIPS

Fully automatic
espresso machines

3100 series

5 Beverages

Integrated milk carafe

Black

AquaClean

EP3550



One touch espresso and cappuccino exactly your way

Get your perfect espresso and cappuccino from fresh beans thanks to the 100% ceramic grinders and select strength, temperature and length via the intuitive display. Your hot cappuccino is a one-touch job, thanks to the Integrated milk jug.

Your fresh coffee experience

- 20,000 cups of finest coffee with durable ceramic grinders
- Adjust your coffee spout to fit any cup
- Smooth milk foam from the carafe frother

A variety of coffees customized to your taste

- Enjoy 5 coffees at your fingertips, including cappuccino
- Adjust the volume, 5 aroma strength and 5 grinder settings
- Decaffeinated with equal zest with the Powder Option
- One-touch Cappuccino with the integrated milk carafe

Enjoy your coffees every day with no hassle

- Enjoy a great coffee with Auto-Rinse & guided descaling
- Designed to maximize capacities in a compact footprint
- Easily operate your machine via the intuitive display
- Clean milk residues after every use with milk clean function
- Up to 5000 cups* without descaling thanks to AquaClean

Highlights

100% ceramic grinders



Our grinders are 100% pure ceramic: extremely hard and precise, so you can enjoy fresh aromatic coffee, for at least 20.000 cups.

Adjustable coffee spout



The adjustable spout on our espresso machines will fit every cup and thus prevents the coffee splashing or cooling down while pouring in your cup. This way your espresso is always served at the right temperature while maintaining a clean machine.

Latte Perfetto Technology



Every coffee you prepare will be topped with a silky, milk layer that beckons the taste buds. The milk carafe froths the milk twice, then pours a splash free creamy layer into your cup at just the right temperature. The carafe can also be stored conveniently in the fridge and it is incredibly hygienic.

5 aromatic coffees



Enjoy your favourite coffees for your special moments. Whether you crave for an espresso, a coffee or a milk based recipe, your fully-automatic espresso machine delivers a perfect in-cup result with no hassle and in no time!

Customize your coffees



This Fully-Automatic machine offers an abundance of indulgent options to customize your beverage to your taste. You can easily personalize and memorize length, strength and temperature for each drink. Feel free to explore, experiment and dream up any drink!

Powder Option




Sometimes it's nice to have the option of a full-bodied, delicious coffee, without the caffeine kick. Thanks to the Powder Option you can make decaffeinated coffee whenever you please.

Integrated milk carafe



Enjoy super creamy cappuccino at the perfect temperature, in the easiest way possible. Simply pour milk into the carafe, plug it into the machine, and select your preferred beverage. Whether it's a cappuccino or frothed milk, your drink will be served within seconds, with a splash-free flow at the ideal temperature.

Auto-Rinse & Guided descaling



This espresso machine automatically cleans its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will prompt when descaling is needed. It will guide you with on-screen messages what you have to do and when.

Specifications

General specifications

Ease of cleaning & maintenance: AquaClean filter compatible

Milk Solution: Integrated Milk Carafe

User Interface: Basic Display

Technical specifications

Capacity milk carafe: 0.5 L

Capacity waste container: 15 servings

Frequency: 50 Hz

Max. cup height: 152 mm

Voltage: 230 V

Color & Finishing: Black

Cord length: >100 cm

Waste container: Frontal access

Water tank: Access from the top

Weight of product: 7.2 kg

Product dimensions: 215 x 330 x 429 mm

Coffee bean capacity: 250 g

Capacity water tank: 1.8 L

Customization

Aroma Strength Settings: 5

Grinder Settings: 5

Pre Brew Aroma control: No

User Profiles: 1

Temperature settings: 3

Coffee and Milk Length: Adjustable

Variety

Beverages: Espresso, Hot water, Cappuccino, Coffee, Milk froth

Coffee Powder Option

Double Cup

Milk Double Cup: No

Other features

Auto-Rinse & Guided descaling

Main Switch ON / OFF button

Quick Heat Boiler

Removable brew group

