

PHILIPS

Fully automatic
espresso machines

Philips 4300 Series

5 Beverages

Classic Milk Frother

Black

TFT display

EP4321/50



5 Delicious coffees from fresh beans, with ease

Thanks to the intuitive display

Enjoy the delicious taste and aroma of coffee from fresh beans, at the perfect temperature, thanks to our AromaExtract system. The new classic milk frother allows you to create a silky smooth cappuccino or a foamy hot milk with ease.

A variety of coffees customized to your taste

- Enjoy 5 coffees at your fingertips
- Delicious milk froth or hot milk with the new steam pipe
- Easy selection of your coffee with the intuitive display
- Adjust aroma strength and volume with the coffee customizer
- Your perfect cup, every time, thanks to 2 user profiles

High quality coffee from fresh beans

- The perfect temperature, aroma and crema cup after cup*
- Easily adjust to your taste with 12-step grinder levels
- 20,000 cups of finest coffee with durable ceramic grinders
- Keep your beans fresh for longer thanks to the aroma seal

Effortless use and cleaning for everyday enjoyment

- Up to 5000 cups* without descaling thanks to AquaClean
- Easy cleaning thanks to fully removable brew group
- Dishwasher safe parts for your convenience

Highlights

5 delicious coffees



Every moment has its own kind of coffee to enjoy. From powerful espresso to indulgent cappuccino, your fully automatic espresso machine delivers a perfect in-cup result without any fuss in no time!

Classic milk frother



The classic milk frother makes it simple to prepare warm, silky-smooth frothed milk for your next cappuccino or foamy hot milk for your caffè latte.

Intuitive display



There's little standing between you and your next delicious cup of coffee with our easy to use display. In a few steps you can customize your fresh-bean flavor and flow smoothly from craving to cup.

Coffee customizer



Make any coffee your own with the coffee customizer's easily adjustable settings for intensity and coffee length.

User profiles

Enjoy coffee you love the same way every time with two user profiles that store your customized recipes. With an extra guest profile, your visitors can savor a coffee exactly the way they like, without changing yours.

Perfect temperature and aroma



The Aroma Extract system intelligently strikes the optimum balance between brewing temperature and aroma extraction by keeping the water temperature between 90 and 98°C, while regulating the water flow rate, so you can enjoy delicious coffees.

12-step grinder adjustment



Our durable ceramic grinders can be adjusted in 12 steps, so you can turn your beans into anything from ultra-fine powder to coarse grindings.

100% ceramic grinders



Our grinders are 100% pure ceramic: extremely hard and precise, so you can enjoy fresh aromatic coffee, for at least 20.000 cups.

AquaClean filter



By changing the filter after being prompted by the machine, you will not need to descale your machine for up to 5000 cups*, while enjoying clear and purified water.

Preserve beans' aroma



The new Aroma seal protects your favorite coffee beans and makes sure they retain their original aroma over time, while reducing the grinder noise.

Specifications

Country of origin

Designed in: Italy
Made in: Romania

General specifications

Ease of cleaning & maintenance: AquaClean filter compatible
Type of display: TFT
Adjustable spout height: 85 - 145 mm
Milk Solution: Classic Milk Frother
Dishwasher safe parts: Classic milk frother, Drip tray

Technical specifications

Capacity waste container: 12 servings
Frequency: 50 Hz
Voltage: 230 V
Color(s): Black
Finishing: Black Glossy
Cord length: 100 cm
Filter compatibility: AquaClean
Waste container: Frontal access

Water tank: Frontal access
Weight of product: 8 kg
Product dimensions: 246x372x433 mm
Coffee bean capacity: 275 g
Capacity water tank: 1.8 L
Pump pressure: 15 bar

Customization

Aroma Strength Settings: 5
Coffee Length: Adjustable
Grinder Settings: 12
Pre Brew Aroma control
User Profiles: 2, Guest
Temperature settings: 3

Variety

Beverages: Espresso, Coffee, Americano, Caff  crema, Ristretto, Milk froth, Hot water
Coffee Powder Option
Double Cup
Milk Double Cup: No

Other features

Removable brew group
Aroma Seal
Guided descaling
AquaClean

Accessories

Included: Measuring scoop, Water hardness test strip, AquaClean filter, Grease tube

Service

2-year guarantee

Sustainability

ECO setting
Power consumption brewing: 1500 W
Recyclable packaging material: > 95%

Bazaarvoice_DA_CO_FAM

S4300: PHI 4300 CMF

