

Institutional Television

EP9125C

## 25" Philips/Magnavox Commercial Television

*(screen size measured diagonally)*

- *Front Control Lockout*
- *Local Preview™ - Channel Guide*
- *SmartMute™*
- *Programmable Channel Blanking*
- *Channel Guide*
- *Auto Power On*
- *Volume Limiter*
- *Marquee Channel™*
- *Audio/Video Muting*
- *Smart Sound™*
- *ESP™ (Energy Savings Programmability)*
- *Spill-Resistant Cabinet*
- *Security Mountable*
- *Consumer Television Convertible*
- *External Speaker Connection*
- *V-Chip Compliant*



20 PB  
Remote



**Setting Industry Standards™**

*Let's make things better.*

**PHILIPS MAGNAVOX**

The EP9125C is a full-featured commercial television designed and manufactured exclusively for the lodging industry.

#### Technical Specifications:

- System: 525 lines per picture, 60 fields per second, interlaced for NTSC 3.58 systems
- Power Source: 90-150Vac, 50/60Hz
- Power Consumption: 75W (avg.)
- Picture Tube: 25" Diagonal, 100°
- Audio Output: 1 x 1.0 Watts
- Speaker Size: 3" round
- Resolution: RF - 370+, TV lines (per picture width - horizontal)
- Operating Temperature: 32°F - 104°F (0°C - 40°C)
- Weight: 71 lbs.
- Operating Humidity: 5% - 100%
- Dimensions (WxHxD): 24 3/8" x 21 3/4" x 20 1/4"
- Closed-Captioning: Compatible with all FCC recognized modes
- Channel Capability: 181 channels
- Audio: 1 x 1.0 Watt, @ 16Ω, @ 5% THD, 50Hz - 12kHz frequency response

#### Input/Output Capabilities:

- Antenna Input: 75Ω VHF/UHF

#### Special Features:

##### Front Control Lockout

Provides the ability to selectively or completely disable front control panel buttons.

##### Local Preview™

Automatically displays channel guide every time television is turned on. After choosing the channel to view, channel guide fades off screen to be displayed again when called up using the remote.

##### SmartMute™

Automatically displays Closed Caption service whenever the user activates the mute function.

##### Programmable Channel Blanking

Provides a means to force the picture to be blanked without affecting the audio. Perfect for audio-only services, such as FM radio.

##### Channel Guide

Provides guests with an onscreen directory listing channel number and network affiliation. Channel guide is accessed via the touch of a single button on the remote.

##### Volume Limiter

Programmable minimum/maximum and turn-on volume range. Forces the monitor/receiver to operate within a user defined volume range, preventing volume adjustments that are too high or too low.

##### Auto Power On

Forces the default power setting to the ON position, preventing sets from being turned off while in use. Additionally, this feature allows all sets to be controlled from a single circuit breaker and forces the set to turn back on automatically after a power interruption.

##### Marquee Channel

Forces the television to a specified channel when turned on. Perfect for in-house advertising or information channels.

##### Audio/Video Muting

Automatically detects a loss of television signal and optionally mutes both audio and video. Prevents annoyance due to snowy picture and static.

##### SmartSound™

Automatic volume leveler. Automatically detects variations in the audio level and adjusts to acceptable levels, minimizing the excessive volume levels often associated with commercial advertising.

##### ESP™ (Energy Saving Programmability)

Energy Saving system that powers television off after a specified period of use. A simple countdown clock can be selectively set to operate from 0-99 hours with automatic clock reset at each power up.

##### Spill-Resistant Cabinet

Reduces the risk of damage to the television in the event liquid is spilled on the cabinet.

##### Security Mountable

Equipped with heavy-duty blocks on the bottom of the cabinet, designed for safe and secure mounting to security brackets.

##### Consumer Television Convertible

Easily converts to true consumer television for aftermarket sales.

##### 20-Button Guest Remote: (not included)

Provides guest access to power, volume, channel selection, mute, closed captioning, channel guide, and sleep timer.

##### Special Setup Remote Transmitter: RG4172BK (not included)


Used during initial setup of televisions, the setup remote allows limited access to critical TV functions such as power, channel up/down, volume, color, tint, brightness, sharpness, etc. Once setup is complete, the setup transmitter is retained in a secure location.



UL listed for commercial use

PHILIPS ITV WEBSITE: <http://www.philipspro.com>

Philips Institutional TV (ITV)  
©1999 Philips Consumer Electronics Company  
A Division of Philips Electronics North America Corporation  
KID Design, 99460, Philips Consumer Electronics Co.



Setup Remote  
Optional  
(RG4172BK)

Specifications subject to change without notice.

Let's make things better.

PHILIPS MAGNAVOX