


Portable MP3-CD player with MAGIC ESP™

- **Plays CD's containing MP3 tracks and regular Audio CD's**
- **Capable of playing over 10 hours of music per MP3-CD**
One MP3-CD can contain over 10 hours of music or more than 150 tracks (maximum 999)
- **MAGIC ESP™ - SHOCK PROOF**
Automatically stores from 45 up to over 100 seconds of music (at 128Kbps) to prevent music interruptions caused by shocks.
- **CD-Rewritable compatible**
Ensures that both CD-Recordable and CD-Rewritable disks, made by any CD-Recorder, can be played.
- **Playback of MP3 (32-320 Kbps) and VBR**
Supports 32 upto 320 Kbps per MP3 track and variable bitrate per MP3 track.
- **10-hour playback with two AA Alkaline batteries**
Powersaving technology extends battery playing time to 10 hours with two regular LR6-size (AA) alkaline batteries.
- **All CD program modes**
Let's you enjoy various CD program modes (shuffle/ repeat track/ repeat all/ introscan). Introscan plays 8 seconds of each track automatically to quickly scan a CD.
- **Headphone, car-kit and AC/DC adapter included**



EXPANIUM

Standard product information

Amplifier/ system

- Output power (in-ear headphone) 2 x 3mW RMS
- 1-Bit D/A converter for pure sound reproduction
- Digital dynamic bass boost
- Rotary volume control
- S/N ratio (A weighted) : >100 dB
- Frequency response : 20 Hz - 20 kHz
- Acoustic feedback

CD player

- Supports the CD-ROM, CD-Recordable and CD-Rewritable in ISO-9660 and Joliet format.
- Playback possibility of 32, 40, 48, 56, 64, 80, 96, 112, 128, 160, 192, 224, 256 and 320 Kbps per MP3 track
- Supports Variable Bit Rate per track
- Supports CD's that contains music tracks with mixed bit rates
- 30-Track programmable, shuffle, repeat 1/all and introscan
- Search forward/backward
- Resume and hold

MAGIC ESP™ (Electronic skip protection)

- **SHOCK PROOF** Automatically stores from 45 up to over 100 seconds of music (at 128Kbps) to prevent music interruptions caused by shocks.

LCD display

- Indications for track, album, time, DBB, CD functions, ESP and battery status

Connections

- Headphone/ line out : stereo, 3.5 mm
- DC in : 4.0 mm, 4.5V, centre '+'

Power supply

- Batteries : 2 x 1.5V, type AA/LR6/UM3 cell
- Battery playing time : 10 hours (Alkaline)
- Automatic power switch-off

General

- Material : High temperature resistant plastic
- Weight : g (excluding batteries)
- Product dimensions : 130 mm W x 32 mm H x 138 mm D
- D-box dimensions : 150 mm W x 95 mm H x 170 mm D
- Master carton dimensions : 166 mm W x 103 mm H x 348 mm D
- Master carton quantity : 2

Accessories

- AC/DC adapter
- Stereo in-ear headphone
- Car cassette adapter
- 4.5V Car cigarette lighter DC/DC adapter

Product highlights

- **Digital dynamic bass boost**
Enhances bass at low, mid and high volume, to give deep, rich sounds.
- **Compact disc audio player**
Compact Disc technology that provides uncompressed superb digital sound quality.
- **Heat resistant body**
Unique composite material enables the CD player to withstand very high temperatures for in-car use.
- **1-Bit D/A converter**
Advanced digital conversion technology ensures crystal-clear sound.
- **Hold**
Locks all buttons electronically to prevent interruption of play or change of program settings.
- **Resume**
Ensures the CD starts precisely from the point it was stopped.
- **Automatic power off**
Automatically switches off the CD player at the end of a compact disc.
- **CD next/ previous**
Plays the next or previous track at the touch of a button
- **Repeat one/ all**
Repeat the current track or the total CD
- **Shuffle**
Plays disc selection randomly, giving you each time a new sequence of tracks
- **30-track programmable**
Stores up to 30 of your favourite tracks for playing back in your order of preference
- **Acoustic feedback**
Confirms any key-push with friendly beep to acknowledges that a command has been given.