

**Standard product information**

**COMPACT DISC PLAYER**

- 3 Disc Changer
- Programmable memory for 40 tracks
- Program Review facility
- Shuffle enables random playing of tracks
- Next and previous keys for track skip
- Frequency range 20-20000 Hz
- Signal-to-noise ratio 90 dB
- Digital Servo Control Mechanism
- CD changer lens
- Time mode

**CASSETTE DECK**

- Dual stereo decks (playback and recording/play)
- High and normal speed dubbing
- CD synchro recording
- Continuous play
- Automatic recording level control
- Automatic tape type selection
- Electronic speed control

**TUNER**

- PLL quartz digital tuner
- 20 random presets
- Up/down single step and search tuning
- Automatic programming of tuner presets
- FM stereo/mono switch and FM stereo broadcasting information
- Wave band selector
- FM antenna wire

**AMPLIFIER**

- 2 x 15 W RMS, 3Ω, ±10% THD
- Dynamic bass boost (4 steps)
- Incredible sound
- CD, tape, tuner and aux sources
- Digital Sound Control (jazz, classic, rock, pop and optimal)
- Visual sound icons

**TIMER**

- Precision quartz controlled clock
- Automatic clock set via RDS
- Wake up timer
- Wake-up with CD, tuner or tape
- Record timer

**LOUDSPEAKER BOXES**

- 2 Way bass reflex
- 5 1/4" woofer
- 2 1/2" tweeter
- Dimensions (mm) (w x h x d) : 200 x 310 x 226 mm

**CONNECTIONS**

- Multimedia/Aux : cinch type sockets
- Stereo headphones : 3.5 mm stereo jack
- Loudspeaker : click-fit connectors

**GENERAL**

- Monoblock configuration
- 12 Key Audio/Video Remote Control
- Trade mode via 'demo' button
- Dimensions with LSB (w x h x d) : 665 x 310 x 360 mm
- Backlit keys

Subject to modification without notice

Printed in Holland

3122 321 7387 2

	/21	/22	/37	/33	/30	/25	/34
Asia Pacific	■	●	■	■	■	■	■
Europe	■	■	●	■	■	■	■
Overseas	●	■	■	■	■	■	■
USA	■	■	■	■	■	■	■
<b>Tuner</b>							
FM 65.81 - 74 MHz							●
FM 87.5 - 108 MHz	●	●	●	●	●	●	●
FM 76 - 90 MHz + CH 1, 2, 3							
MW 522 - 1602 kHz	●	●	●	●	●	●	●
LW 153 - 279 kHz		●				●	●
FM 75Ω coax input	●	●	●		●	●	
FM 300Ω Clickfit				●			
RDS with clock set		●					

	/21	/22	/37	/33	/30	/25	/34
Asia Pacific	■	●	■	■	■	■	■
Europe	■	■	●	■	■	■	■
Overseas	●	■	■	■	■	■	■
USA	■	■	■	■	■	■	■
<b>Karaoke</b>							
Dual Mic	●	●				●	
<b>Mains Supply</b>							
100V / 60 Hz							
120V / 60 Hz				●			
230V / 50 Hz			●			●	
120 / 230V - 50 / 60 Hz	●	●			●	●	
<b>General</b>							
Made in Sticker	●	●	●	●	●	●	●



**PHILIPS**