

PHILIPS

Handheld vacuum cleaner

4.8 V



FC6051



Easy cleaning anywhere

Precision nose piece

The specially designed Philips FC6051 (4.8 V) cleans anywhere easily, thanks to its extended nose piece. The FC6051 has 4 powerful rechargeable batteries that give you the freedom of efficient cordless cleaning wherever you want.

Easily cleans in corners and along curves

- Extended nose piece

Always at hand

- Slim charging base for wall and table

Cordless cleaning power wherever you want

- Powerful rechargeable batteries

Lasting suction power

- 2-stage filter system prevents early clogging

Easily cleans delicate surfaces and narrow spaces

- Brush tool and crevice tool

Highlights

Extended nose piece



The Philips Mini Vac FC6051 series has a long, narrow nose especially designed for precision cleaning. The extended nose piece makes it easy to clean in corners and along curves.

Slim charging base for wall and table



You can store the Philips Mini Vac on the convenient charging base, mounted on a wall or placed on a table. This means the Mini Vac, with its powerful rechargeable battery, is always ready when you are.

Powerful rechargeable batteries



The Philips Mini Vac's rechargeable battery gives you the freedom of cordless cleaning wherever you want.

2-stage filter system prevents early clogging



The Philips Mini Vac's 2-stage filtration system ensures that, once inside, dirt cannot escape. The first filter blocks most dirt, while the pleated second filter traps the finer dust particles.

Brush tool and crevice tool



The Philips Mini Vac comes with a number of accessories to tackle any job with ease. The soft brush attachment is gentle on delicate surfaces and the crevice tool lets you clean even those awkward, hard-to-reach places.

Specifications

Design

Colour: Raven black

Filtration

Dust capacity: 0.3 l

Filter system: 2-stage

Nozzles and accessories

Other accessories: Charging base

Performance

Airflow (max): 650 l/min

Battery voltage: 4.8 V

Charging time: 16-18 hour(s)

Noise level (Lc IEC): 80 dB

Runtime: 9 minute(s)

Suction power (max): 9 W

Vacuum (max): 2.4 kPa

Usability

Special features: Charging indication

Weight and dimensions

Dimensions of A-box (L x W x H): 402 x 397 x 453 mm

Appliances per A-box: 6

Dimensions of packaging (L x W x H): 419 x 124 x 190 mm

