

# PHILIPS

## Mite Cleaning Vacuum Cleaner

Removes dust and mites

Reduces Allergens

Soft surfaces

450 W



FC6230/01



## Safely and efficiently removes dust and mites

### For an allergy friendly home

Philips Mite Cleaner removes dust and mites easily and effectively from soft surfaces. Its three functions make the cleaning of soft surfaces effortless. It also reduces allergens, for an allergy friendly home. Equipped with an UV-Light.

#### Compact and easy to use

- Warning signal to ensure that dust container is well placed
- 4 meter cord allows for easy reach
- Easy to operate dust container for quick disposal of dirt
- Small brush is included to keep your product clean

#### Safe UV light

- Three safety sensors automatically shut off UV light
- Includes Philips UV light

#### Safely and effectively removes dust and mites

- Three different cleaning modes to suit your needs
- EPA 12 filter ensures dust will not escape again
- 450 W motor for powerful removal of dust and mites
- Suitable for cleaning all soft surfaces in your home
- Powerful vibrating pads to loosen up dirt

# Highlights

### Auto off for UV light

Three safety sensors detect if product is in contact with a surface or not. It will automatically shut off the UV light to ensure safe operation, always.


### Cleaning mode selection

Three different modes allow you to select particular settings for cleaning specific surfaces, to better suit your cleaning needs.

### Dust container sensor

Warning signal to ensure that dust container is well placed.

### Easy reach



4 meter cord allows for easy reach.

### EPA Filter



The EPA 12 Filters captures 99.5% of fine dust particles while filtering the exhaust air. This keeps dust securely within the container, preventing secondary contamination.

### Philips UV Light

Includes Philips UV light.

### Powerful Vacuuming Motor

The combination of a powerful 450 W motor and 8.2 cm suction vent will ensure the effective removal of dust and mites from soft surfaces, reducing the allergens in your home.

### Small Maintenance Brush



Small brush is included to keep your product clean.

### Suitable for all soft surfaces



Effectively and safely remove dust and mites from beds, sofas, plush toys, cushions and all other soft surfaces for an allergy friendly home.

### Vibrating pads



Three padding feet vibrate at a high speed of 3600 rpm to vigorously loosen dust and dirt from inside soft surfaces.

### Easy to empty dust container



An easy to operate dust container makes the disposal of dust both simple and hygienic.



### British Allergy Foundation

Seal of Approval This product helps you to manage the symptoms of your allergy, sensitivity or intolerance.

# Specifications

## Performance

Input power (IEC): 450 W  
Punch Speed: 3600 rpm

## Usability

Cord length: 4 m  
Dust full indicator

## Design

Color: Blue

## Filtration

Exhaust filter: EPA 12 filter  
Motor filter: Microfilter

## Nozzles and accessories

Accessories included: Brush

## Weight and dimensions

Dimensions of product (LxWxH): 425 x 300 x 190 mm  
Weight of product: 3 kg

