

# PHILIPS

Dust Mite Hand Held Vacuum Cleaner, Anti-Allergen

Filters 99% of dust mites

UV light to help detect dust mites

Vibrating pad to dislodge mites

Dust container for quick disposal of dirt

FC6232



## Safely and efficiently removes dust and mites

### For an allergy-friendly home

Philips Mite Cleaner removes dust and mites easily and effectively from soft surfaces. Its three functions make cleaning soft surfaces effortless. It also reduces allergens, for an allergy-friendly home. Equipped with a UV Light.

#### **Safely and effectively removes dust and mites**

- Powerful vibrating pads to loosen dirt
- 450-W motor for powerful removal of dust and mites
- Suitable for cleaning all soft surfaces in your home
- Three different cleaning modes to suit your needs
- EPA 12 filter ensures dust will not escape again

#### **Safe UV light**

- Includes Philips UV light
- Three safety sensors automatically shut off UV light

#### **Compact and easy to use**

- Warning signal to ensure that dust container is properly placed
- Easy-to-operate dust container for quick disposal of dirt
- Small brush is included to keep your product clean
- 5-metre cord allows for easy reach

# Highlights

## Vibrating pads



Three padded feet vibrate at a high speed of 3600 rpm to vigorously loosen dust and dirt from inside soft surfaces.

## Powerful Vacuuming Motor

The combination of a powerful 450-W motor and 8.2-cm suction vent will ensure the effective removal of dust and mites from soft surfaces, reducing the allergens in your home.

## Suitable for all soft surfaces



Effectively and safely remove dust and mites from beds, sofas, plush toys, cushions and all other soft surfaces for an allergy-friendly home.

## Cleaning mode selection

Three different modes allow you to select particular settings for cleaning specific surfaces, to better suit your cleaning needs.

## Philips UV Light

Includes Philips UV light.

## Auto-off for UV light

Three safety sensors detect whether the product is in contact with a surface or not. It will automatically shut off the UV light to ensure safe operation, always.

## Dust container sensor

Warning signal to ensure that dust container is properly placed.

## Easy to empty dust container



An easy-to-operate dust container makes the disposal of dust both simple and hygienic.

## Small Maintenance Brush



Small brush is included to keep your product clean.

## Easy reach

5-metre cord allows for easy reach.

## EPA Filter

The EPA 12 filter captures 99.5% of fine dust particles while filtering the exhaust air. This keeps dust securely within the container, preventing secondary contamination.

# Specifications

## Performance

Input power (IEC): 450 W  
Punch Speed: 3600 rpm

## Usability

Cord length: 5 m  
Dust full indicator

## Design

Colour: Shining gold

## Filtration

Exhaust filter: EPA 12 filter  
Motor filter: Micro filter

## Nozzles and accessories

Accessories included: Brush

## Weight and dimensions

Dimensions of product (LxWxH): 425 x 300 x 190 mm  
Weight of product: 3 kg



## British Allergy Foundation

Seal of Approval This product helps you to manage the symptoms of your allergy, sensitivity or intolerance.