

PHILIPS

Vacuum cleaner and
Mopping System

PowerPro Aqua

3-in-1

Vacuum and mop

18 V



FC6404/01



Vacuums and mops in one stroke

Always at hand to quickly clean daily messes

The new cordless (Li-Ion) PowerPro Aqua is a 3in1 powerful tool to deal with daily messes. A bagless vacuum cleaner for all floors, a handheld vacuum cleaner for surfaces like sofa, chair or corners and a mopping system to clean damp dirt.

Cleans everyday messes with vacuum and mop

- PowerCyclone Technology for high vacuum cleaning performance
- New mopping system with optimal wetness for all hard floors
- Handheld for vacuuming furniture and hard to reach corners
- TriActive Turbo nozzle for powerful performance on carpets
- 3 layer filter technology captures micro particles

Always at hand and convenient for daily usage

- The nozzle's motorized brush thoroughly removes pet hair
- Cordless cleaning: freedom to clean everywhere
- Bagless: One-step empty dust bucket
- Powerful 18 V Lithium Ion battery for long runtime
- Suitable to use on all floors
- Instant click on/off mopping system to do wet cleaning
- High maneuverability and light weight for easy handling

Highlights

PowerCyclone Technology



The PowerCyclone technology delivers high vacuum cleaning results in one go. Air enters rapidly into the PowerCyclone and is accelerated further through the curved air pass to effectively separate dust from air.

Innovative mopping system



The unique mopping system controls the water release to maintain optimal wetness for all hard floors throughout the cleaning.

Handheld included



Handheld for vacuuming furniture and hard to reach corners

TriActive Turbo nozzle



The TriActive Turbo nozzle delivers powerful performance on hard floors and carpets. The motorized brush and the optimized airflow pick up all dirt and fluff in one go.

3 layer filter




3 layer washable filter can capture >90% of allergens like pollen, pet hair and dust, for a clean air.

Effective on Animal Hair



Thanks to the TriActive Turbo nozzle with a motorized brush, you can now remove animal hair from couches, cushions and other fabrics. Ideal for pet owners.

Cordless cleaning



Without the cord, you are free to clean wherever you want on every type of floor.

One-step empty dust bucket



The new bagless PowerPro Aqua vacuum cleaner dispose dust from the dust bucket without touching the dirt.

Powerful Lithium Ion battery



Cordless cleaning with powerful 18 V Lithium Ion battery for 40 min run time. The cable is not a barrier anymore and you can easily clean different rooms without hassle.

Suitable to use on all floors



Vacuum all hard floors and carpets. Click on the water tank to mop all types of hard floors.

Specifications

Performance

Battery type: Li-Ion

Battery voltage: 18 V

Charging time: 5 hour(s)

Mopping element: Unique mopping system

Runtime: 40 minute(s)

Surface coverage per tank: 50 m²

Sound power level: 83 dB

Usability

Clean water tank capacity (max): 0.2 L

Detergents that can be used: clear detergent or just water

Design

Color: Electric aqua

Design features: On-off

Filtration

Dust capacity: 0.6 L

Exhaust filter: Microfilter

Filter system: 3-stage cyclonic action

Nozzles and accessories

Accessories included: Crevice tool, 2 microfiber pads, 2-in-1 brush

Standard nozzle: TriActive Turbo Nozzle

Sustainability

Packaging: > 90% recycled materials

User manual: 100% recycled paper

Weight and dimensions

Dimensions of product (LxWxH):

250x180x1160 mm

Weight of product: 4.7 kg

