

PHILIPS

Cordless Stick
vacuum cleaner

SpeedPro

Slim nozzle with side brushes

18V, up to 40 min

2-in-1: vacuum & handheld

FC6721/01



Fast, with powerful reach

The new SpeedPro cordless vacuum cleaner provides a fast clean, with powerful reach. It's equipped with a slim design nozzle with side brushes for effective dirt pick-up, which can reach far, even under lower furniture.

Fast clean, with powerful reach

- Captures up to 90% of dust and dirt in each stroke
- Fast reach everywhere, even under low furniture
- Two speed settings to suit different floors and dirt types

Uninterrupted, effective cleaning

- Up to 40 min of cleaning power, with 18V Li-Ion batteries
- Integrated handheld unit, crevice tool and brush
- Unique dust bucket design empties without dust clouds

High air speed for long-lasting performance

- PowerBlade motor is engineered for high air speed
- PowerCyclone 7 maintains strong performance for longer
- Washable filter ensures high air speed for longer*

Highlights

Slim nozzle with side brushes



The slim nozzle profile with side brushes is designed for up to 90% pick-up of dust and dirt in each stroke, even in hard to reach areas, such as under lower furniture.

Fast reach everywhere



SpeedPro is flexible and easy to maneuver. The dust bucket is on top, which allows for a lower angle and even goes fully flat on the floor to reach under low furniture.

Two speed settings



Two speed settings to suit different floors and dirt types.

Up to 40 minutes runtime



High performance 18V lithium ion batteries provide up to 40 minutes in normal mode and 20 minutes in turbo mode, before you recharge.

Integrated accessories



Accessories are simple to use with one click. The detachable handheld unit makes SpeedPro two devices in one. The brush attachment is integrated into the tube so it's always at hand to clean ceilings and shelves.

Hygienic emptying



The vacuum cleaner's dust bucket is easily removed and emptied hygienically without causing any dust cloud.

PowerBlade motor



PowerBlade motor is engineered for high air speed, to enable powerful, precise pick-up at nozzle level.

PowerCyclone 7



PowerCyclone 7 technology immediately separates dust from air, to maintain strong performance for longer.

Washable filter



The filter system captures up to 99% of pollen and mold spores, returning clean air back to the motor ensuring high air speed and longer-lasting performance.

Specifications

Performance

Airflow (max): Up to 800 l/min

Battery type: Li-Ion

Battery voltage: 18 V

Charging time: 5 hour(s)

Runtime: 40 minute(s)

Runtime (turbo): 20 minute(s)

Sound power level: 80 dB

Usability

Carrying handle: Top

Wheel type: Rubber

Design

Design features: 2-in-1

Color: Monza Red

Filtration

Dust capacity: 0.4 L

Motor filter: Washable filter*

Nozzles and accessories

Standard nozzle: Slim nozzle with side brushes

Accessories included: AC power adaptor,
Crevice tool, Integrated brush

Weight and dimensions

Weight of product: 2.4 kg

Sustainability

Packaging: > 90% recycled materials

