

PHILIPS

Cordless Stick vacuum cleaner

SpeedPro Aqua

180° suction nozzle

21.6V, up to 50 min

3-in-1: vacuum, mop & handheld

Mini turbo brush



FC6729/01



Fast. 3-in-1 with vacuum, mop and handheld

The new SpeedPro Aqua cordless vacuum cleaner provides a fast clean, with powerful reach, even in the toughest spots. It is equipped with the 180° suction nozzle for precise dirt pick-up and a unique vacuum and mop system.

Fast clean, with powerful reach

- Captures up to 98% of dust and dirt in each stroke
- LEDs in the nozzle reveal hidden dust and dirt

Uninterrupted 3-in-1 cleaning

- Vacuum, mop and handheld, with up to 99% of bacteria removal
- For multiple dirt types, with AquaBoost for tougher dirt
- Up to 50 min of cleaning power, with 21.6V Li-Ion batteries
- Integrated handheld unit, crevice tool and brush
- Fast reach everywhere, even under low furniture
- Unique dust bucket design empties without dust clouds
- Mini turbo brush for fast clean of soft surfaces

High air speed for long-lasting performance

- PowerBlade motor is engineered for high air speed
- PowerCyclone 7 maintains strong performance for longer
- Washable filter ensures high air speed for longer*

Highlights

180° suction nozzle



180° suction nozzle is designed for precise and powerful pick-up of up to 98% of dust and dirt in each stroke, on all floor types, even in those hard to reach spots.

LED nozzle



Dust, fluff, hair and crumbs are easy to spot and captured due to the LED lights in the SpeedPro nozzle. LEDs in the nozzle reveal hidden dust and dirt, on the go.

Vacuum and mop system



The unique vacuum and mop system helps remove up to 99% of bacteria in one go. Controlled water release maintains optimal wetness for all hard floors throughout the cleaning. The microfiber pads can be washed by hand or in the washing machine.

Up to 50 minutes runtime



High performance 21.6V lithium ion batteries provide up to 50 minutes in normal mode and 22 minutes in turbo mode, before you recharge.

Integrated accessories



Accessories are simple to use with one click. The detachable handheld unit makes SpeedPro two devices in one. The brush attachment is integrated into the tube so it's always at hand to clean ceilings and shelves.

Fast reach everywhere



SpeedPro is flexible and easy to maneuver. The dust bucket is on top, which allows for a lower angle and even goes fully flat on the floor to reach under low furniture.

Mini turbo brush



The mini turbo brush is ideal for removing pet hair from upholstery, seats and carpets. It is compact, powerful and effective.

PowerBlade motor



PowerBlade motor is engineered for high air speed, to enable powerful, precise pick-up at nozzle level.

PowerCyclone 7



PowerCyclone 7 technology immediately separates dust from air, to maintain strong performance for longer.

AquaBoost



AquaBoost mode to clean tougher dirt faster.

Specifications

Performance

Airflow (max): Up to 800 l/min
Battery type: Li-Ion
Battery voltage: 21.6 V
Charging time: 5 hour(s)
Runtime: 50 minute(s)
Runtime (turbo): 22 minute(s)
Sound power level: 80 dB
Surface coverage per tank: 60 m²

Usability

Carrying handle: Top
Clean water tank capacity (max): 0.28 L
Detergents that can be used: clear detergent or just water
Wheel type: Rubber

Design

Design features: 3-in-1
Color: Deep Opal Metallic

Filtration

Dust capacity: 0.4 L
Motor filter: Washable filter*

Nozzles and accessories

Standard nozzle: Vacuum and Mop
Additional nozzle: 180° suction nozzle, Mini turbo brush
Accessories included: AC power adaptor, Crevice tool, Micro fiber pad, Integrated brush, Wall-mount docking, Water tank

Weight and dimensions

Weight of product: 2.45 kg

Sustainability

Packaging: > 90% recycled materials

