

# PHILIPS

Cordless Stick vacuum cleaner

SpeedPro Max Aqua

360° suction nozzle

25.2 V, up to 75 min runtime

3-in-1: vacuum, mop & handheld

TurboPet Nozzle



FC6904/01



## Fastest cordless vacuum\* with 3-in-1 cleaning

Finish faster with our 3-in-1 cordless vacuum. Our powerful 360° suction nozzle captures dust and dirt faster from all sides. From hard floors to carpets; make every move count. Unique vacuum & mop system tackles multiple dirt types at once.

### Uninterrupted 3-in-1 cleaning

- 3-in-1: 360° suction nozzle, vacuum & mop system, handheld
- For multiple dust types, incl. AquaBoost for tougher dirt
- Integrated handheld unit, crevice tool and brush
- Fast reach everywhere, even under low furniture

### Unrivalled speed

- 360° suction nozzle captures dust and dirt faster
- LED nozzle reveals hidden dust and dirt
- Up to 75 min\* of powerful cleaning with 25.2V Li-Ion battery

### Unmatched airflow

- PowerCyclone 8 - our most powerful bagless technology
- PowerBlade digital motor creates high airflow (>1000 L/min)
- The Triple filtration system ensures high airflow for longer



[asimpleswitch.com](https://asimpleswitch.com)

# Highlights

## 360° suction nozzle



360° suction nozzle captures dust and dirt faster

## Up to 75 minutes runtime



High performance 25.2 V lithium ion batteries provide up to 75 minutes Eco runtime, 35 min in normal mode and 25 min in Turbo mode before you recharge.

## PowerBlade digital motor



PowerBlade is a digital motor engineered for unmatched, high airflow (>1000 L/min) that produces 360° suction at the nozzle. Register at Philips.com within 3 months of purchase and enjoy a free 5-year motor warranty!

## Vacuum and Mop system



The unique vacuum and mop system controls the water release to maintain optimal wetness for all hard floors throughout the cleaning. The microfiber pads can be washed by hand or in washing machine.

## Fast reach everywhere



SpeedPro Max is flexible and easy to maneuver. The dust bucket is on top, which allows for a lower angle and even goes fully flat on the floor to reach under low furniture.

## PowerCyclone 8 technology




PowerCyclone 8 technology – our best bagless vacuum cleaning technology now in a cordless stick, to keep stronger suction for longer.

## Integrated accessories



Accessories are simple to use with one click. The detachable handheld unit makes SpeedPro Max two devices in one. The brush attachment is integrated into tube so it's always at hand.

## LED nozzle



Dust, fluff, hair and crumbs are easy to spot and eliminated with LED lights in the SpeedPro Max nozzle. LED nozzle reveals even the hidden dirt.



[asimpleswitch.com](https://www.asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Performance

**Battery type:** Li-Ion  
**Battery voltage:** 25.2 V  
**Charging time:** 5 hour(s)  
**Runtime:** 75 minute(s)  
**Runtime (turbo):** 25 minute(s)  
**Sound power level:** 84 dB  
**Surface coverage per tank:** 60 m<sup>2</sup>  
**Airflow (max):** 1000 l/min

## Usability

**Clean water tank capacity (max):** 0.28 L  
**Detergents that can be used:** clear detergent or just water

## Design

**Color:** Electric Aqua

## Filtration

**Dust capacity:** 0.6 L  
**Motor filter:** Washable filter

## Nozzles and accessories

**Accessories included:** AC power adaptor, Micro fiber pad, Integrated brush, Extra filter  
**Additional nozzle:** TurboPet nozzle, 360° suction nozzle  
**Standard nozzle:** Vacuum and Mop

## Sustainability

**Packaging:** > 90% recycled materials  
**User manual:** 100% recycled paper

## Weight and dimensions

**Weight of product:** 2.732 kg

