

PHILIPS

AquaTrio Pro

3-in-1: vacuums, mops & dries

Triple-Acceleration Technology

Visible wet cleaning

All hard floors

FC7088/71



Vacuums, mops and dries in one go

Visible wet cleaning for hard floors

AquaTrio Pro simultaneously vacuums, mops and dries, saving up to 50% time and effort*. Powerfull and gentle microfiber brushes to effectively remove dirt & stains. For perfect visible wet cleaning results on all hard floors**.

Easy to use and efficient

- Cleans more than 60m² with one water tank
- LED indicators to inform when action is required
- Save up to 50% energy. Save up to 70% water*
- Self-cleaning appliance with flushing tray
- Effective with cold/warm tap water, with/without detergent
- Ideal for all hard floors**
- Floor dries 50% faster than regular mopping

Constant cleaning performance

- Fast rotating brushes clean themselves while in use
- Separate clean and dirty water tanks

Revolutionary technology for perfect results

- Removes up to 99% of bacteria*** and reduces allergens
- 2 micro-fiber brushes remove all dirt, dust and grime
- Allergy friendly quality tested by ECARF



Highlights

Triple-Acceleration Technology



- Vacuums: powerful Aqua Cyclone pulls and removes all spills, dirt and dust - Mops: counter-rotating microfiber brushes apply a mist of clean water to efficiently lift dirt and grime. All dirt is dissolved in water and captured in a separate tank. - Dries: brush rotation speed creates airflow that leaves the floor virtually dry


Hygienic cleaning results

AquaTrio Pro removes up to 99% of all bacteria*** and reduces allergens. Because of the separation of a clean and dirty water tank all dust and allergens will be trapped in the dirty water tank.

Tap water

AquaTrio Pro gives excellent results using just cold or warm tap water. If required, you can also add detergent of your choice but use always a low-foaming or non-foaming floor cleaning detergent which is suitable for your hard floor.

Fast rotating brushes



Powerful micro-fiber brushes rotate at 6700 rpm to effectively remove all spills, dust and dirt while adapting to the different shapes of the floor and even cleaning in crevices.

Separate water tanks




Separate clean and dirty water tanks ensure that you always mop with clean water, all dirt and allergens are contained in the dirty water tank.

Floor dries 50% faster




Floor dries up to 50% faster compared to regular mopping.

For all hard floors**



Perfect for all hard floors (suitable for wet mopping): wood, parquet, laminate, vinyl/linoleum, ceramics/tiles, marble/natural stone.

Cleans more than 60m²



One full tank containing 700ml cleans more than 60m² of hard floor; cleaning large areas using only a minimal amount of water.

Self cleaning brushes

Brushes clean themselves during use. The centrifugal forces spin dirt and water picked up from the floor out of the brushes and into the dirty water tank. For optimal cleaning performance replace the AquaTrio Pro brushes every 6 months (FC8054).

Save 50% energy/70% water*



Highly-efficient power usage saves you up to 50% in energy consumption compared to vacuuming. You also use up to 70% less water compared to wet mopping.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO₂ emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Performance

Cleaning Technology: Triple-Acceleration Technology
Input power (IEC): Max 500 W
Mopping element: 2 microfiber rotating brushes
Surface coverage per tank: 60 m²

Usability

Refill indicator
Carrying handle: Front
Clean water tank capacity (max): 0.65 L
Detergents that can be used: clear detergent or just water

Dirty water tank capacity (max): 0.8 L
Tank full indicator
Action radius: 9.5 m
Cord length: 8 m

Design

Color: Anthracite metallic

Nozzles and accessories

Accessories included: Flushing tray

Steam Management

Steam temp. at nozzle: >100 °C

Sustainability

Packaging: > 90% recycled materials
User manual: 100% recycled paper

Weight and dimensions

Dimensions of product (LxWxH): 305 x 320 x 1150 mm
Dimensions of packaging (LxWxH): 790 x 390 x 395 mm
Weight incl. packaging: 10.8 kg
Weight of product: 6.7 kg

